

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P205352

Luminaire Tested: **LD6B60D010TE EU6B60709050 6LBNLI1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P205352
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B60D010TE EU6B60709050 6LBNI1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
NARROW DISTRIBUTION WITH SPECULAR CLEAR TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4138.3 lumens
Efficiency: N/A
Efficacy: 66.2 lumens/watt
Spacing Criteria (0/90/45): 0.53 / 0.53 / 0.58
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 62.48
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P205352

CATALOG NUMBER: LD6B60D010TE EU6B60709050 6LBNLI1

Luminous Intensity Polar Plot





TEST NUMBER: P205352

CATALOG NUMBER: LD6B60D010TE EU6B60709050 6LBNLI1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			0
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			100
1	114	112	109	107	112	109	107	106		105	104	102			102	101	99			95
2	109	105	101	98	107	103	100	97		100	97	95			97	95	93			89
3	105	99	94	91	103	97	93	90		95	91	89			93	90	87			85
4	100	93	88	85	98	92	88	84		90	86	83			88	85	82			80
5	96	88	83	79	94	87	83	79		86	82	78			84	81	78			76
6	92	84	79	75	90	83	78	75		82	77	74			80	76	74			72
7	88	80	74	71	87	79	74	71		78	73	70			77	73	70			68
8	84	76	71	67	83	75	70	67		74	70	67			73	69	66			65
9	81	73	67	64	80	72	67	64		71	67	63			70	66	63			62
10	78	69	64	61	77	69	64	61		68	64	61			67	63	60			59

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P205352

CATALOG NUMBER: LD6B60D010TE EU6B60709050 6LBNLI1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	783.4	18.9
10°-20°	1406.1	34.0
20°-30°	1136.9	27.5
30°-40°	654.9	15.8
40°-50°	138.5	3.3
50°-60°	11.9	0.3
60°-70°	6.0	0.1
70°-80°	0.8	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3326.3	80.4
0°-40°	3981.2	96.2
0°-60°	4131.6	99.8
0°-90°	4138.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4138.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	9422	
5°	8778	783
15°	5108	1406
25°	2452	1137
35°	1038	655
45°	149	138
55°	12	12
65°	6	6
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P205352

CATALOG NUMBER: LD6B60D010TE EU6B60709050 6LBNLI1

CANDELA DISTRIBUTION (FULL):

	0°
0°	9422.0
2.5°	9308.6
5°	8777.5
7.5°	8013.7
10°	7076.9
12.5°	6116.2
15°	5107.8
17.5°	4135.2
20°	3425.1
22.5°	2882.1
25°	2452.5
27.5°	2088.5
30°	1760.3
32.5°	1396.3
35°	1038.3
37.5°	722.0
40°	471.4
42.5°	286.4
45°	149.2
47.5°	59.7
50°	17.9
52.5°	17.9
55°	11.9
57.5°	11.9
60°	6.0
62.5°	6.0
65°	6.0
67.5°	6.0
70°	6.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)