

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P683908

Luminaire Tested: **LX6C100D010 EX6C1009040 6LBNH**

Issue Date: 2/15/2022



Test Information

Test Method: LM-79-08
Report Number: P683908
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P203666)
Test Lab: INNOVATION CENTER
Issue Date: 2/15/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX6C100D010 EX6C1009040 6LBNH
Description: 6 INCH 10000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 4000K, 90CRI LEDS
AND 6LBN TRIM WITH H FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6615.0 lumens
Efficiency: N/A
Efficacy: 57.8 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.84
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 114.4
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P683908

CATALOG NUMBER: LX6C100D010 EX6C1009040 6LBNH

Luminous Intensity Polar Plot





TEST NUMBER: P683908

CATALOG NUMBER: LX6C100D010 EX6C1009040 6LBNH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	109	106	104	104	103	101	101	99	98	97	96	95	93			
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	83	79	77	75			
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70			
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	65			
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61			
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58			
9	76	66	60	56	75	66	60	56	65	59	56	64	59	56	63	59	55	54			
10	72	62	57	53	71	62	57	53	61	56	53	60	56	52	60	55	52	51			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	464864
5°	453356
10°	418318
15°	370360
20°	321573
25°	275054
30°	226769
35°	149332
40°	80279
45°	35539
50°	14413
55°	10399
60°	6600
65°	4722
70°	3895
75°	2563
80°	3820
85°	0



TEST NUMBER: P683908

CATALOG NUMBER: LX6C100D010 EX6C1009040 6LBNH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	762.5	11.5
10°-20°	1818.5	27.5
20°-30°	2083.3	31.5
30°-40°	1399.7	21.2
40°-50°	399.9	6.0
50°-60°	97.9	1.5
60°-70°	37.2	0.6
70°-80°	14.4	0.2
80°-90°	1.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4664.3	70.5
0°-40°	6064.0	91.7
0°-60°	6561.8	99.2
0°-90°	6615.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6615.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8480	
5°	8238	763
15°	6526	1818
25°	4547	2083
35°	2231	1400
45°	458	400
55°	109	98
65°	36	37
75°	12	14
85°	0	2
90°	0	



TEST NUMBER: P683908

CATALOG NUMBER: LX6C100D010 EX6C1009040 6LBNH

CANDELA DISTRIBUTION (FULL):

	0°
0°	8479.8
2.5°	8419.5
5°	8238.4
7.5°	7912.6
10°	7514.8
12.5°	7007.9
15°	6525.7
17.5°	6019.2
20°	5512.2
22.5°	5030.0
25°	4547.3
27.5°	4101.0
30°	3582.4
32.5°	2894.8
35°	2231.4
37.5°	1628.3
40°	1121.8
42.5°	735.7
45°	458.4
47.5°	277.3
50°	169.0
52.5°	132.6
55°	108.8
57.5°	84.5
60°	60.2
62.5°	48.1
65°	36.4
67.5°	24.3
70°	24.3
72.5°	12.1
75°	12.1
77.5°	12.1
80°	12.1
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)