

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P683945

Luminaire Tested: **LX6C120D010 EX6C1209027 6LBMH**

Issue Date: 2/15/2022



Test Information

Test Method: LM-79-08
Report Number: P683945
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P203254)
Test Lab: INNOVATION CENTER
Issue Date: 2/15/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX6C120D010 EX6C1209027 6LBMH
Description: 6 INCH 12000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 2700K, 90CRI LEDS
AND 6LBM TRIM WITH H FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8712.0 lumens
Efficiency: N/A
Efficacy: 61.2 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.93
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 142.3
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P683945

CATALOG NUMBER: LX6C120D010 EX6C1209027 6LBMH

Luminous Intensity Polar Plot





TEST NUMBER: P683945

CATALOG NUMBER: LX6C120D010 EX6C1209027 6LBMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	92	92	92	92
2	107	102	97	93	105	100	96	92	97	93	90	94	91	88	91	89	87	85	85	85	85
3	101	94	88	84	99	92	87	84	90	86	82	87	84	81	85	82	80	78	78	78	78
4	95	87	81	76	93	86	80	76	84	79	75	82	78	74	80	76	73	72	72	72	72
5	90	81	75	70	88	80	74	70	78	73	69	76	72	68	75	71	68	66	66	66	66
6	85	75	69	64	83	75	69	64	73	68	64	72	67	63	70	66	63	61	61	61	61
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57	57	57	57
8	76	66	60	55	75	65	59	55	64	59	55	63	58	55	62	58	54	53	53	53	53
9	72	62	56	51	71	61	55	51	60	55	51	60	55	51	59	54	51	49	49	49	49
10	69	58	52	48	68	58	52	48	57	52	48	56	51	48	55	51	48	46	46	46	46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	472654
5°	464191
10°	440473
15°	413050
20°	384672
25°	354438
30°	295330
35°	208151
40°	132656
45°	79109
50°	46694
55°	29705
60°	20459
65°	14528
70°	10002
75°	7900
80°	3883
85°	0



TEST NUMBER: P683945

CATALOG NUMBER: LX6C120D010 EX6C1209027 6LBMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	788.3	9.0
10°-20°	2039.4	23.4
20°-30°	2642.5	30.3
30°-40°	1961.8	22.5
40°-50°	828.2	9.5
50°-60°	294.0	3.4
60°-70°	113.5	1.3
70°-80°	39.3	0.5
80°-90°	5.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5470.2	62.8
0°-40°	7432.0	85.3
0°-60°	8554.2	98.2
0°-90°	8712.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8712.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8622	
5°	8435	788
15°	7278	2039
25°	5860	2642
35°	3110	1962
45°	1020	828
55°	311	294
65°	112	114
75°	37	39
85°	0	5
90°	0	



TEST NUMBER: P683945

CATALOG NUMBER: LX6C120D010 EX6C1209027 6LBMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	8621.9
2.5°	8596.8
5°	8435.3
7.5°	8198.6
10°	7912.8
12.5°	7601.5
15°	7277.9
17.5°	6917.4
20°	6593.8
22.5°	6258.0
25°	5859.7
27.5°	5312.2
30°	4665.5
32.5°	3906.3
35°	3110.3
37.5°	2438.6
40°	1853.7
42.5°	1380.8
45°	1020.4
47.5°	746.4
50°	547.5
52.5°	410.5
55°	310.8
57.5°	236.2
60°	186.6
62.5°	137.0
65°	112.0
67.5°	86.9
70°	62.4
72.5°	49.6
75°	37.3
77.5°	25.0
80°	12.3
82.5°	12.3
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)