

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P683946

Luminaire Tested: **LX6C120D010 EX6C1209027 6LBNH**

Issue Date: 2/15/2022

**Test Information**

Test Method: LM-79-08  
Report Number: P683946  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P203666)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/15/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LX6C120D010 EX6C1209027 6LBNH  
Description: 6 INCH 12000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 2700K, 90CRI LEDS  
AND 6LBN TRIM WITH H FINISH  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7494.9 lumens  
Efficiency: N/A  
Efficacy: 52.7 lumens/watt  
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.84  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 142.3  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P683946

CATALOG NUMBER: LX6C120D010 EX6C1209027 6LBNH

### Luminous Intensity Polar Plot





TEST NUMBER: P683946

CATALOG NUMBER: LX6C120D010 EX6C1209027 6LBNH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	109	106	104	104	103	101	101	99	98	97	96	95	93			
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	83	79	77	75			
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70			
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	65			
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61			
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58			
9	76	66	60	56	75	66	60	56	65	59	56	64	59	56	63	59	55	54			
10	72	62	57	53	71	62	57	53	61	56	53	60	56	52	60	55	52	51			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	526701
5°	513668
10°	473973
15°	419628
20°	364353
25°	311643
30°	256932
35°	169195
40°	90956
45°	40268
50°	16332
55°	11775
60°	7477
65°	5344
70°	4408
75°	2902
80°	4325
85°	0



TEST NUMBER: P683946

CATALOG NUMBER: LX6C120D010 EX6C1209027 6LBNH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	864.0	11.5
10°-20°	2060.4	27.5
20°-30°	2360.4	31.5
30°-40°	1585.9	21.2
40°-50°	453.1	6.0
50°-60°	110.9	1.5
60°-70°	42.2	0.6
70°-80°	16.3	0.2
80°-90°	1.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5284.8	70.5
0°-40°	6870.6	91.7
0°-60°	7434.6	99.2
0°-90°	7494.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7494.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	9608	
5°	9334	864
15°	7394	2060
25°	5152	2360
35°	2528	1586
45°	519	453
55°	123	111
65°	41	42
75°	14	16
85°	0	2
90°	0	



TEST NUMBER: P683946

CATALOG NUMBER: LX6C120D010 EX6C1209027 6LBNH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	9607.8
2.5°	9539.6
5°	9334.4
7.5°	8965.2
10°	8514.6
12.5°	7940.2
15°	7393.8
17.5°	6819.9
20°	6245.5
22.5°	5699.1
25°	5152.2
27.5°	4646.6
30°	4058.9
32.5°	3279.8
35°	2528.2
37.5°	1844.9
40°	1271.0
42.5°	833.6
45°	519.4
47.5°	314.2
50°	191.5
52.5°	150.2
55°	123.2
57.5°	95.7
60°	68.2
62.5°	54.5
65°	41.2
67.5°	27.5
70°	27.5
72.5°	13.7
75°	13.7
77.5°	13.7
80°	13.7
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)