

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P684798

Luminaire Tested: **LX6C120D010 EX61209030 6LBSLI**

Issue Date: 2/15/2022



Test Information

Test Method: LM-79-08
Report Number: P684798
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205419)
Test Lab: INNOVATION CENTER
Issue Date: 2/15/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX6C120D010 EX61209030 6LBSLI
Description: 6 INCH 12000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS
AND 6LBS TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 13358.9 lumens
Efficiency: N/A
Efficacy: 93.9 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 1.04
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 142.3
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P684798

CATALOG NUMBER: LX6C120D010 EX61209030 6LBSLI

Luminous Intensity Polar Plot





TEST NUMBER: P684798

CATALOG NUMBER: LX6C120D010 EX61209030 6LBSLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|---|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | | 0 | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | |
| 1 | 111 | 107 | 104 | 101 | 109 | 105 | 102 | 99 | 101 | 99 | 96 | 97 | 95 | 93 | 94 | 92 | 91 | 89 | | | |
| 2 | 103 | 96 | 91 | 86 | 100 | 94 | 89 | 85 | 91 | 87 | 83 | 88 | 84 | 81 | 85 | 82 | 79 | 77 | | | |
| 3 | 95 | 86 | 79 | 74 | 93 | 85 | 78 | 73 | 82 | 76 | 72 | 79 | 75 | 71 | 77 | 73 | 70 | 68 | | | |
| 4 | 88 | 78 | 70 | 64 | 86 | 77 | 69 | 64 | 74 | 68 | 63 | 72 | 67 | 62 | 70 | 65 | 62 | 60 | | | |
| 5 | 82 | 71 | 63 | 57 | 80 | 70 | 62 | 57 | 67 | 61 | 56 | 66 | 60 | 55 | 64 | 59 | 55 | 53 | | | |
| 6 | 76 | 64 | 56 | 51 | 74 | 63 | 56 | 51 | 62 | 55 | 50 | 60 | 54 | 50 | 59 | 53 | 49 | 47 | | | |
| 7 | 71 | 59 | 51 | 46 | 70 | 58 | 51 | 45 | 57 | 50 | 45 | 55 | 49 | 45 | 54 | 49 | 45 | 43 | | | |
| 8 | 67 | 54 | 47 | 41 | 65 | 54 | 46 | 41 | 52 | 46 | 41 | 51 | 45 | 41 | 50 | 45 | 41 | 39 | | | |
| 9 | 63 | 50 | 43 | 38 | 61 | 50 | 43 | 38 | 49 | 42 | 38 | 48 | 42 | 37 | 47 | 41 | 37 | 36 | | | |
| 10 | 59 | 47 | 40 | 35 | 58 | 46 | 39 | 35 | 45 | 39 | 35 | 45 | 39 | 34 | 44 | 38 | 34 | 33 | | | |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|--------|
| | 0° |
| 0° | 462145 |
| 5° | 456878 |
| 10° | 433715 |
| 15° | 400314 |
| 20° | 365957 |
| 25° | 331368 |
| 30° | 301857 |
| 35° | 279243 |
| 40° | 261010 |
| 45° | 243149 |
| 50° | 221494 |
| 55° | 193962 |
| 60° | 161818 |
| 65° | 127017 |
| 70° | 88717 |
| 75° | 48081 |
| 80° | 8997 |
| 85° | 0 |



TEST NUMBER: P684798

CATALOG NUMBER: LX6C120D010 EX61209030 6LBSLI

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|---------|-----------|
| 0°-10° | 776.8 | 5.8 |
| 10°-20° | 1977.6 | 14.8 |
| 20°-30° | 2521.9 | 18.9 |
| 30°-40° | 2615.3 | 19.6 |
| 40°-50° | 2409.8 | 18.0 |
| 50°-60° | 1812.7 | 13.6 |
| 60°-70° | 978.4 | 7.3 |
| 70°-80° | 262.5 | 2.0 |
| 80°-90° | 3.9 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 5276.4 | 39.5 |
| 0°-40° | 7891.7 | 59.1 |
| 0°-60° | 12114.2 | 90.7 |
| 0°-90° | 13358.9 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 13358.9 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 8430 | |
| 5° | 8302 | 777 |
| 15° | 7054 | 1978 |
| 25° | 5478 | 2522 |
| 35° | 4173 | 2615 |
| 45° | 3136 | 2410 |
| 55° | 2029 | 1813 |
| 65° | 979 | 978 |
| 75° | 227 | 262 |
| 85° | 0 | 4 |
| 90° | 0 | |



TEST NUMBER: P684798

CATALOG NUMBER: LX6C120D010 EX61209030 6LBSLI

CANDELA DISTRIBUTION (FULL):

| 0° | |
|-------|--------|
| 0° | 8430.2 |
| 2.5° | 8401.9 |
| 5° | 8302.4 |
| 7.5° | 8117.9 |
| 10° | 7791.4 |
| 12.5° | 7465.2 |
| 15° | 7053.5 |
| 17.5° | 6670.5 |
| 20° | 6273.0 |
| 22.5° | 5861.5 |
| 25° | 5478.3 |
| 27.5° | 5109.3 |
| 30° | 4768.6 |
| 32.5° | 4456.3 |
| 35° | 4172.6 |
| 37.5° | 3902.8 |
| 40° | 3647.3 |
| 42.5° | 3377.9 |
| 45° | 3136.3 |
| 47.5° | 2866.9 |
| 50° | 2597.1 |
| 52.5° | 2313.4 |
| 55° | 2029.4 |
| 57.5° | 1745.7 |
| 60° | 1475.9 |
| 62.5° | 1220.4 |
| 65° | 979.2 |
| 67.5° | 752.2 |
| 70° | 553.5 |
| 72.5° | 383.2 |
| 75° | 227.0 |
| 77.5° | 99.2 |
| 80° | 28.5 |
| 82.5° | 0.0 |
| 85° | 0.0 |
| 87.5° | 0.0 |
| 90° | 0.0 |



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)