

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P684802

Luminaire Tested: **LX6C120D010 EX61209035 6LBNLI**

Issue Date: 2/14/2022

Test Information

Test Method: LM-79-08
Report Number: P684802
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205310)
Test Lab: INNOVATION CENTER
Issue Date: 2/14/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX6C120D010 EX61209035 6LBNLI
Description: 6 INCH 12000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3500K, 90CRI LEDS
AND 6LBN TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9990.1 lumens
Efficiency: N/A
Efficacy: 70.2 lumens/watt
Spacing Criteria (0/90/45): 0.53 / 0.53 / 0.58
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 142.3
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P684802

CATALOG NUMBER: LX6C120D010 EX61209035 6LBNLI

Luminous Intensity Polar Plot





TEST NUMBER: P684802

CATALOG NUMBER: LX6C120D010 EX61209035 6LBNLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	112	109	107	112	109	107	106	105	104	102	102	101	99	98	97	96	95			
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	89			
3	105	99	94	91	103	97	93	90	95	91	89	93	90	87	90	88	86	85			
4	100	93	88	85	98	92	88	84	90	86	83	88	85	82	86	84	81	80			
5	96	88	83	79	94	87	83	79	86	82	78	84	81	78	83	80	77	76			
6	92	84	79	75	90	83	78	75	82	77	74	80	76	74	79	76	73	72			
7	88	80	74	71	87	79	74	71	78	73	70	77	73	70	76	72	69	68			
8	84	76	71	67	83	75	70	67	74	70	67	73	69	66	73	69	66	65			
9	81	73	67	64	80	72	67	64	71	67	63	70	66	63	70	66	63	62			
10	78	69	64	61	77	69	64	61	68	64	61	67	63	60	67	63	60	59			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1246879
5°	1166044
10°	950996
15°	699811
20°	482354
25°	358097
30°	268984
35°	167736
40°	81424
45°	27933
50°	3667
55°	2772
60°	1590
65°	1881
70°	2324
75°	0
80°	0
85°	0



TEST NUMBER: P684802

CATALOG NUMBER: LX6C120D010 EX61209035 6LBNLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1891.1	18.9
10°-20°	3394.3	34.0
20°-30°	2744.4	27.5
30°-40°	1580.9	15.8
40°-50°	334.2	3.3
50°-60°	28.9	0.3
60°-70°	14.4	0.1
70°-80°	1.9	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	8029.8	80.4
0°-40°	9610.7	96.2
0°-60°	9973.8	99.8
0°-90°	9990.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9990.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	22745	
5°	21189	###
15°	12331	3394
25°	5920	2744
35°	2506	1581
45°	360	334
55°	29	29
65°	14	14
75°	0	2
85°	0	0
90°	0	



TEST NUMBER: P684802

CATALOG NUMBER: LX6C120D010 EX61209035 6LBNLI

CANDELA DISTRIBUTION (FULL):

0°	
0°	22744.9
2.5°	22471.6
5°	21189.4
7.5°	19345.6
10°	17084.0
12.5°	14765.0
15°	12330.6
17.5°	9982.6
20°	8268.2
22.5°	6957.5
25°	5920.2
27.5°	5041.8
30°	4249.3
32.5°	3370.8
35°	2506.4
37.5°	1742.9
40°	1137.8
42.5°	691.6
45°	360.3
47.5°	143.9
50°	43.0
52.5°	43.0
55°	29.0
57.5°	29.0
60°	14.5
62.5°	14.5
65°	14.5
67.5°	14.5
70°	14.5
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)