

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204950

Luminaire Tested: **LD6B70D010TE EU6B60708027 6LBCSMB1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P204950  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD6B70D010TE EU6B60708027 6LBCSMB1  
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT  
SHALLOW DISTRIBUTION WITH CAST MATTE BLACK TRIM  
SINGLE DRIVER D010TE  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6292.1 lumens  
Efficiency: N/A  
Efficacy: 79.2 lumens/watt  
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 79.45  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P204950

CATALOG NUMBER: LD6B70D010TE EU6B60708027 6LBCSMB1

### Luminous Intensity Polar Plot





TEST NUMBER: P204950

CATALOG NUMBER: LD6B70D010TE EU6B60708027 6LBCSMB1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	111	107	103	100	108	104	101	98	100	98	95	96	94	92	93	91	90	88				88
2	102	95	89	84	99	93	87	83	89	85	81	86	82	79	83	80	77	75				75
3	93	84	77	71	91	83	76	70	80	74	69	77	72	68	74	70	67	65				65
4	86	75	67	61	84	74	66	61	71	65	60	69	63	59	67	62	58	56				56
5	79	67	59	53	77	66	59	53	64	57	52	62	56	52	61	55	51	49				49
6	74	61	53	47	72	60	52	46	58	51	46	57	50	46	55	50	45	43				43
7	68	55	47	41	67	55	47	41	53	46	41	52	45	41	50	45	40	39				39
8	64	51	43	37	62	50	42	37	49	42	37	48	41	37	46	41	36	35				35
9	60	47	39	33	58	46	39	33	45	38	33	44	38	33	43	37	33	31				31
10	56	43	35	30	55	43	35	30	42	35	30	41	34	30	40	34	30	28				28

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P204950

CATALOG NUMBER: LD6B70D010TE EU6B60708027 6LBCSMB1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	251.3	4.0
10°-20°	715.9	11.4
20°-30°	1076.3	17.1
30°-40°	1277.0	20.3
40°-50°	1263.7	20.1
50°-60°	992.6	15.8
60°-70°	556.6	8.8
70°-80°	156.3	2.5
80°-90°	2.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2043.5	32.5
0°-40°	3320.5	52.8
0°-60°	5576.9	88.6
0°-90°	6292.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6292.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2657	
5°	2652	251
15°	2540	716
25°	2337	1076
35°	2048	1277
45°	1646	1264
55°	1119	993
65°	555	557
75°	135	156
85°	0	2
90°	0	



TEST NUMBER: P204950

CATALOG NUMBER: LD6B70D010TE EU6B60708027 6LBCSMB1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2656.9
2.5°	2647.9
5°	2652.4
7.5°	2629.8
10°	2602.8
12.5°	2571.2
15°	2539.6
17.5°	2499.0
20°	2444.9
22.5°	2390.8
25°	2336.6
27.5°	2278.0
30°	2201.3
32.5°	2124.6
35°	2047.9
37.5°	1957.7
40°	1854.0
42.5°	1754.7
45°	1646.5
47.5°	1524.7
50°	1398.4
52.5°	1254.0
55°	1118.7
57.5°	965.3
60°	821.0
62.5°	690.2
65°	554.8
67.5°	437.6
70°	324.8
72.5°	221.0
75°	135.3
77.5°	67.7
80°	18.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)