

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203918

Luminaire Tested: **LD6B70D010TE EU6B60708027 6LBNGPH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203918
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B70D010TE EU6B60708027 6LBNGPH1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
NARROW DISTRIBUTION WITH GRAPHITE HAZE TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3410.1 lumens
Efficiency: N/A
Efficacy: 42.9 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.88
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 79.45
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203918

CATALOG NUMBER: LD6B70D010TE EU6B60708027 6LBNGPH1

Luminous Intensity Polar Plot





TEST NUMBER: P203918

CATALOG NUMBER: LD6B70D010TE EU6B60708027 6LBNGPH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	114	111	108	106	111	109	106	104	105	103	101	101	100	98	97	96	95	94																			
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	92	91	89	87																			
3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	88	85	83	81																			
4	97	90	84	80	96	89	84	80	87	82	79	85	81	78	83	80	77	76																			
5	93	84	78	74	91	83	78	74	82	77	73	80	76	73	78	75	72	70																			
6	88	79	73	69	86	78	73	69	77	72	68	75	71	68	74	70	67	66																			
7	84	74	68	64	82	74	68	64	72	67	64	71	67	63	70	66	63	62																			
8	79	70	64	60	78	69	64	60	68	63	60	67	63	59	66	62	59	58																			
9	76	66	60	56	75	66	60	56	65	60	56	64	59	56	63	59	56	54																			
10	72	63	57	53	71	62	57	53	61	56	53	61	56	53	60	55	52	51																			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203918

CATALOG NUMBER: LD6B70D010TE EU6B60708027 6LBNGPH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	375.2	11.0
10°-20°	925.4	27.1
20°-30°	1121.3	32.9
30°-40°	764.1	22.4
40°-50°	182.0	5.3
50°-60°	28.5	0.8
60°-70°	10.6	0.3
70°-80°	3.1	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2421.9	71.0
0°-40°	3186.1	93.4
0°-60°	3396.5	99.6
0°-90°	3410.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3410.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4145	
5°	4028	375
15°	3313	925
25°	2450	1121
35°	1221	764
45°	194	182
55°	31	28
65°	8	11
75°	0	3
85°	0	0
90°	0	



TEST NUMBER: P203918

CATALOG NUMBER: LD6B70D010TE EU6B60708027 6LBNGPH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	4145.0
2.5°	4121.7
5°	4028.4
7.5°	3904.0
10°	3725.1
12.5°	3522.9
15°	3312.9
17.5°	3095.2
20°	2877.4
22.5°	2659.7
25°	2449.7
27.5°	2255.3
30°	1975.3
32.5°	1609.8
35°	1221.0
37.5°	871.0
40°	575.5
42.5°	357.7
45°	194.4
47.5°	101.1
50°	54.4
52.5°	38.9
55°	31.1
57.5°	23.3
60°	15.6
62.5°	15.6
65°	7.8
67.5°	7.8
70°	7.8
72.5°	7.8
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)