

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P683965

Luminaire Tested: **LX6C120D010 EX6C1209035 6LBWH**

Issue Date: 2/15/2022



Test Information

Test Method: LM-79-08
Report Number: P683965
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P202739)
Test Lab: INNOVATION CENTER
Issue Date: 2/15/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX6C120D010 EX6C1209035 6LBWH
Description: 6 INCH 12000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3500K, 90CRI LEDS
AND 6LBW TRIM WITH H FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 11116.0 lumens
Efficiency: N/A
Efficacy: 78.1 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.16
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 142.3
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P683965

CATALOG NUMBER: LX6C120D010 EX6C1209035 6LBWH

Luminous Intensity Polar Plot





TEST NUMBER: P683965

CATALOG NUMBER: LX6C120D010 EX6C1209035 6LBWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	103	110	107	104	101	103	100	98	99	97	95	95	94	93	91			91
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81			81
3	98	90	84	79	96	89	83	78	86	81	77	83	79	76	81	78	75	73			73
4	92	82	75	70	90	81	75	70	79	73	69	77	72	68	75	71	67	65			65
5	86	75	68	63	84	74	68	63	72	66	62	71	65	61	69	64	61	59			59
6	80	69	62	57	78	68	61	56	67	61	56	65	60	56	64	59	55	53			53
7	75	64	56	51	73	63	56	51	62	55	51	60	55	51	59	54	50	49			49
8	70	59	52	47	69	58	51	47	57	51	46	56	50	46	55	50	46	44			44
9	66	55	48	43	65	54	47	43	53	47	43	52	47	42	51	46	42	41			41
10	62	51	44	40	61	50	44	39	50	43	39	49	43	39	48	43	39	38			38

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	375842
5°	375714
10°	372822
15°	370326
20°	364685
25°	356349
30°	335526
35°	303650
40°	253561
45°	194291
50°	137599
55°	86754
60°	48932
65°	31767
70°	20741
75°	15250
80°	9155
85°	9120



TEST NUMBER: P683965

CATALOG NUMBER: LX6C120D010 EX6C1209035 6LBWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	647.6	5.8
10°-20°	1837.4	16.5
20°-30°	2694.1	24.2
30°-40°	2803.9	25.2
40°-50°	1939.9	17.5
50°-60°	844.7	7.6
60°-70°	259.0	2.3
70°-80°	77.7	0.7
80°-90°	11.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5179.1	46.6
0°-40°	7983.0	71.8
0°-60°	10767.5	96.9
0°-90°	11116.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	11116.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6856	
5°	6828	648
15°	6525	1837
25°	5891	2694
35°	4537	2804
45°	2506	1940
55°	908	845
65°	245	259
75°	72	78
85°	14	12
90°	0	



TEST NUMBER: P683965

CATALOG NUMBER: LX6C120D010 EX6C1209035 6LBWH

CANDELA DISTRIBUTION (FULL):

0°	
0°	6855.9
2.5°	6870.4
5°	6827.5
7.5°	6770.0
10°	6697.5
12.5°	6625.5
15°	6525.1
17.5°	6395.1
20°	6251.2
22.5°	6092.7
25°	5891.3
27.5°	5631.9
30°	5300.5
32.5°	4954.6
35°	4537.3
37.5°	4076.5
40°	3543.2
42.5°	3010.4
45°	2506.1
47.5°	2030.7
50°	1613.4
52.5°	1224.6
55°	907.7
57.5°	648.3
60°	446.3
62.5°	331.4
65°	244.9
67.5°	187.4
70°	129.4
72.5°	101.0
75°	72.0
77.5°	43.0
80°	29.0
82.5°	14.5
85°	14.5
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)