

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P205254

Luminaire Tested: **LD6B70D010TE EU6B60708027 6LBWLI1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P205254  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD6B70D010TE EU6B60708027 6LBWLI1  
Description: PORTFOLIO 6 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT  
WIDE DISTRIBUTION WITH SPECULAR CLEAR TRIM  
SINGLE DRIVER D010TE  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6851.3 lumens  
Efficiency: N/A  
Efficacy: 86.2 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.18  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 79.45  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P205254

CATALOG NUMBER: LD6B70D010TE EU6B60708027 6LBWLI1

### Luminous Intensity Polar Plot





TEST NUMBER: P205254

CATALOG NUMBER: LD6B70D010TE EU6B60708027 6LBWLI1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	107	104	110	107	105	103	103	101	99	100	98	97	96	95	94	92			92
2	106	101	96	92	104	99	95	91	95	92	89	92	90	87	90	87	85	83			83
3	100	92	87	82	97	91	86	81	88	84	80	86	82	79	83	80	77	76			76
4	93	85	78	73	92	84	78	73	81	76	72	79	75	71	77	74	70	69			69
5	88	78	71	66	86	77	71	66	75	70	65	73	69	65	72	68	64	63			63
6	82	72	65	60	81	71	65	60	70	64	59	68	63	59	67	62	59	57			57
7	77	67	60	55	76	66	59	55	65	59	54	63	58	54	62	57	54	52			52
8	73	62	55	50	71	61	55	50	60	54	50	59	54	50	58	53	49	48			48
9	69	57	51	46	67	57	50	46	56	50	46	55	50	46	54	49	46	44			44
10	65	54	47	43	64	53	47	42	52	46	42	51	46	42	51	46	42	41			41

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P205254

CATALOG NUMBER: LD6B70D010TE EU6B60708027 6LBWLI1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	412.9	6.0
10°-20°	1241.1	18.1
20°-30°	1870.8	27.3
30°-40°	1914.9	27.9
40°-50°	1115.6	16.3
50°-60°	256.3	3.7
60°-70°	31.5	0.5
70°-80°	8.2	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3524.8	51.4
0°-40°	5439.7	79.4
0°-60°	6811.6	99.4
0°-90°	6851.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6851.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4280	
5°	4303	413
15°	4397	1241
25°	4101	1871
35°	3107	1915
45°	1437	1116
55°	249	256
65°	23	31
75°	8	8
85°	0	0
90°	0	



TEST NUMBER: P205254

CATALOG NUMBER: LD6B70D010TE EU6B60708027 6LBWLI1

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	4280.1
2.5°	4272.3
5°	4303.4
7.5°	4334.5
10°	4373.3
12.5°	4381.1
15°	4396.6
17.5°	4381.1
20°	4342.3
22.5°	4218.0
25°	4101.4
27.5°	3915.0
30°	3674.2
32.5°	3425.6
35°	3107.2
37.5°	2749.8
40°	2353.7
42.5°	1910.9
45°	1437.1
47.5°	1002.1
50°	660.3
52.5°	419.5
55°	248.6
57.5°	132.1
60°	69.9
62.5°	38.8
65°	23.3
67.5°	23.3
70°	15.5
72.5°	7.8
75°	7.8
77.5°	7.8
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)