

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204853

Luminaire Tested: **LD6B70D010TE EU6B60709027 6LBCSMW1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P204853  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD6B70D010TE EU6B60709027 6LBCSMW1  
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT  
SHALLOW DISTRIBUTION WITH CAST MATTE WHITE TRIM  
SINGLE DRIVER D010TE  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6394.4 lumens  
Efficiency: N/A  
Efficacy: 80.5 lumens/watt  
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 79.45  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P204853

CATALOG NUMBER: LD6B70D010TE EU6B60709027 6LBCSMW1

### Luminous Intensity Polar Plot





TEST NUMBER: P204853

CATALOG NUMBER: LD6B70D010TE EU6B60709027 6LBSCMW1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	110	106	102	99	108	104	100	97	100	97	94	96	93	91	92	90	89	87			
2	101	94	87	82	99	92	86	81	88	84	79	85	81	78	82	79	76	74			
3	93	83	75	70	90	81	74	69	79	73	68	76	71	67	73	69	65	63			
4	85	74	66	60	83	73	65	59	70	64	58	68	62	58	66	61	57	55			
5	79	66	58	52	77	65	57	51	63	56	51	61	55	50	60	54	50	48			
6	73	60	52	45	71	59	51	45	57	50	45	56	49	44	54	49	44	42			
7	68	55	46	40	66	54	46	40	52	45	40	51	44	40	50	44	39	37			
8	63	50	42	36	61	49	41	36	48	41	36	47	40	36	46	40	35	33			
9	59	46	38	33	57	45	38	32	44	37	32	43	37	32	42	36	32	30			
10	55	42	35	30	54	42	34	30	41	34	29	40	34	29	39	33	29	27			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P204853

CATALOG NUMBER: LD6B70D010TE EU6B60709027 6LBCSMW1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	247.4	3.9
10°-20°	704.5	11.0
20°-30°	1059.7	16.6
30°-40°	1255.9	19.6
40°-50°	1249.8	19.5
50°-60°	1007.5	15.8
60°-70°	609.5	9.5
70°-80°	226.3	3.5
80°-90°	33.7	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2011.6	31.5
0°-40°	3267.5	51.1
0°-60°	5524.9	86.4
0°-90°	6394.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6394.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2612	
5°	2600	247
15°	2495	704
25°	2302	1060
35°	2011	1256
45°	1627	1250
55°	1124	1008
65°	612	609
75°	205	226
85°	27	34
90°	0	



TEST NUMBER: P204853

CATALOG NUMBER: LD6B70D010TE EU6B60709027 6LBCSMW1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2611.7
2.5°	2611.7
5°	2600.0
7.5°	2592.3
10°	2569.0
12.5°	2530.3
15°	2495.4
17.5°	2456.7
20°	2410.2
22.5°	2363.7
25°	2301.7
27.5°	2235.8
30°	2162.2
32.5°	2092.4
35°	2011.1
37.5°	1925.8
40°	1825.1
42.5°	1728.2
45°	1627.4
47.5°	1515.1
50°	1391.1
52.5°	1263.2
55°	1123.7
57.5°	999.7
60°	860.2
62.5°	736.2
65°	612.2
67.5°	496.0
70°	387.5
72.5°	290.6
75°	205.4
77.5°	131.7
80°	77.5
82.5°	46.5
85°	27.1
87.5°	11.6
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)