

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203409

Luminaire Tested: **LD6B70D010TE EU6B60709027 6LBMWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203409
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B70D010TE EU6B60709027 6LBMWH1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH WHEAT TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4595.6 lumens
Efficiency: N/A
Efficacy: 57.8 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.85
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 79.45
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203409

CATALOG NUMBER: LD6B70D010TE EU6B60709027 6LBMWH1

Luminous Intensity Polar Plot





TEST NUMBER: P203409

CATALOG NUMBER: LD6B70D010TE EU6B60709027 6LBMWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR	0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																		
	1	114	111	108	106	111	109	106	104	105	103	101	101	100	98	97	96	95	94																		
	2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	92	91	89	87																		
	3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	88	85	83	81																		
	4	97	90	85	80	96	89	84	80	87	82	79	85	81	78	83	80	77	76																		
	5	93	84	79	74	91	83	78	74	82	77	73	80	76	73	78	75	72	71																		
	6	88	79	73	69	87	78	73	69	77	72	68	76	71	68	74	70	67	66																		
	7	84	75	69	64	82	74	68	64	73	68	64	71	67	64	70	66	63	62																		
	8	80	70	64	60	78	70	64	60	69	64	60	68	63	60	67	62	59	58																		
	9	76	66	61	57	75	66	60	57	65	60	56	64	59	56	63	59	56	55																		
	10	72	63	57	53	71	62	57	53	62	57	53	61	56	53	60	56	53	52																		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203409

CATALOG NUMBER: LD6B70D010TE EU6B60709027 6LBMWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	524.1	11.4
10°-20°	1286.7	28.0
20°-30°	1488.8	32.4
30°-40°	951.6	20.7
40°-50°	269.8	5.9
50°-60°	48.2	1.0
60°-70°	19.7	0.4
70°-80°	6.7	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3299.6	71.8
0°-40°	4251.2	92.5
0°-60°	4569.2	99.4
0°-90°	4595.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4595.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5733	
5°	5631	524
15°	4615	1287
25°	3285	1489
35°	1502	952
45°	313	270
55°	45	48
65°	19	20
75°	6	7
85°	0	0
90°	0	



TEST NUMBER: P203409

CATALOG NUMBER: LD6B70D010TE EU6B60709027 6LBMWH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	5733.1
2.5°	5726.7
5°	5630.9
7.5°	5458.3
10°	5215.4
12.5°	4934.2
15°	4614.6
17.5°	4282.3
20°	3956.3
22.5°	3636.7
25°	3285.2
27.5°	2901.7
30°	2473.5
32.5°	1994.1
35°	1502.0
37.5°	1086.5
40°	754.2
42.5°	498.5
45°	313.2
47.5°	185.4
50°	108.7
52.5°	63.9
55°	44.7
57.5°	38.3
60°	32.0
62.5°	25.6
65°	19.2
67.5°	12.8
70°	12.8
72.5°	6.4
75°	6.4
77.5°	6.4
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)