

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P683990

Luminaire Tested: **LX6C130D010 EX6C1309027 6LBNH**

Issue Date: 2/15/2022



**Test Information**

Test Method: LM-79-08  
Report Number: P683990  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P203666)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/15/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LX6C130D010 EX6C1309027 6LBNH  
Description: 6 INCH 13000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 2700K, 90CRI LEDS  
AND 6LBN TRIM WITH H FINISH  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 8246.9 lumens  
Efficiency: N/A  
Efficacy: 57.2 lumens/watt  
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.84  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 144.3  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P683990

CATALOG NUMBER: LX6C130D010 EX6C1309027 6LBNH

### Luminous Intensity Polar Plot





TEST NUMBER: P683990

CATALOG NUMBER: LX6C130D010 EX6C1309027 6LBNH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	109	106	104	104	103	101	101	99	98	97	96	95	93			
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	83	79	77	75			
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70			
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	65			
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61			
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58			
9	76	66	60	56	75	66	60	56	65	59	56	64	59	56	63	59	55	54			
10	72	62	57	53	71	62	57	53	61	56	53	60	56	52	60	55	52	51			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	579548
5°	565203
10°	521522
15°	461728
20°	400907
25°	342915
30°	282714
35°	186173
40°	100080
45°	44307
50°	17970
55°	12960
60°	8234
65°	5889
70°	4841
75°	3198
80°	4767
85°	0



TEST NUMBER: P683990

CATALOG NUMBER: LX6C130D010 EX6C1309027 6LBNH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	950.7	11.5
10°-20°	2267.1	27.5
20°-30°	2597.2	31.5
30°-40°	1745.0	21.2
40°-50°	498.5	6.0
50°-60°	122.0	1.5
60°-70°	46.4	0.6
70°-80°	17.9	0.2
80°-90°	2.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5815.0	70.5
0°-40°	7560.0	91.7
0°-60°	8180.6	99.2
0°-90°	8246.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8246.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	10572	
5°	10271	951
15°	8136	2267
25°	5669	2597
35°	2782	1745
45°	572	499
55°	136	122
65°	45	46
75°	15	18
85°	0	2
90°	0	



TEST NUMBER: P683990

CATALOG NUMBER: LX6C130D010 EX6C1309027 6LBNH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	10571.8
2.5°	10496.7
5°	10270.9
7.5°	9864.7
10°	9368.8
12.5°	8736.8
15°	8135.6
17.5°	7504.2
20°	6872.1
22.5°	6270.9
25°	5669.2
27.5°	5112.8
30°	4466.2
32.5°	3608.9
35°	2781.9
37.5°	2030.0
40°	1398.5
42.5°	917.2
45°	571.5
47.5°	345.7
50°	210.7
52.5°	165.3
55°	135.6
57.5°	105.3
60°	75.1
62.5°	60.0
65°	45.4
67.5°	30.2
70°	30.2
72.5°	15.1
75°	15.1
77.5°	15.1
80°	15.1
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)