

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P205464

Luminaire Tested: **LD6B70D010TE EU6B60709027 6LBSLI1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P205464
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B70D010TE EU6B60709027 6LBSLI1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH SPECULAR CLEAR TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6276.5 lumens
Efficiency: N/A
Efficacy: 79.0 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 1.04
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 79.45
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P205464

CATALOG NUMBER: LD6B70D010TE EU6B60709027 6LBSLI1

Luminous Intensity Polar Plot





TEST NUMBER: P205464

CATALOG NUMBER: LD6B70D010TE EU6B60709027 6LBSLI1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	107	104	101	109	105	102	99	101	99	96	97	95	93	94	92	91	89		
2	103	96	91	86	100	94	89	85	91	87	83	88	84	81	85	82	79	77		
3	95	86	79	74	93	85	78	73	82	76	72	79	75	71	77	73	70	68		
4	88	78	70	64	86	77	69	64	74	68	63	72	67	62	70	65	62	60		
5	82	71	63	57	80	70	62	57	67	61	56	66	60	55	64	59	55	53		
6	76	64	56	51	74	63	56	51	62	55	50	60	54	50	59	53	49	47		
7	71	59	51	46	70	58	51	45	57	50	45	55	49	45	54	49	45	43		
8	67	54	47	41	65	54	46	41	52	46	41	51	45	41	50	45	41	39		
9	63	50	43	38	61	50	43	38	49	42	38	48	42	37	47	41	37	36		
10	59	47	40	35	58	46	39	35	45	39	35	45	39	34	44	38	34	33		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P205464

CATALOG NUMBER: LD6B70D010TE EU6B60709027 6LBSLI1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	365.0	5.8
10°-20°	929.1	14.8
20°-30°	1184.8	18.9
30°-40°	1228.8	19.6
40°-50°	1132.2	18.0
50°-60°	851.7	13.6
60°-70°	459.7	7.3
70°-80°	123.3	2.0
80°-90°	1.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2479.0	39.5
0°-40°	3707.7	59.1
0°-60°	5691.6	90.7
0°-90°	6276.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6276.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3961	
5°	3901	365
15°	3314	929
25°	2574	1185
35°	1960	1229
45°	1474	1132
55°	954	852
65°	460	460
75°	107	123
85°	0	2
90°	0	



TEST NUMBER: P205464

CATALOG NUMBER: LD6B70D010TE EU6B60709027 6LBSLI1

CANDELA DISTRIBUTION (FULL):

	0°
0°	3960.8
2.5°	3947.4
5°	3900.7
7.5°	3814.1
10°	3660.7
12.5°	3507.3
15°	3314.0
17.5°	3133.9
20°	2947.2
22.5°	2753.9
25°	2573.8
27.5°	2400.5
30°	2240.4
32.5°	2093.7
35°	1960.4
37.5°	1833.7
40°	1713.7
42.5°	1587.0
45°	1473.6
47.5°	1346.9
50°	1220.2
52.5°	1086.9
55°	953.5
57.5°	820.2
60°	693.5
62.5°	573.4
65°	460.1
67.5°	353.4
70°	260.0
72.5°	180.0
75°	106.7
77.5°	46.7
80°	13.3
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)