

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P205053

Luminaire Tested: **LD6B70D010TE EU6B60708030 6LBCSMMS1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P205053
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B70D010TE EU6B60708030 6LBCSMMS1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH CAST MATTE METALLIC SILVER TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7289.7 lumens
Efficiency: N/A
Efficacy: 91.8 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.27
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 79.45
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P205053

CATALOG NUMBER: LD6B70D010TE EU6B60708030 6LBCSMMS1

Luminous Intensity Polar Plot





TEST NUMBER: P205053

CATALOG NUMBER: LD6B70D010TE EU6B60708030 6LBCSMMS1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	107	103	100	108	105	101	98	100	98	95	97	94	92	93	91	90	88			88
2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76			76
3	94	85	77	72	92	83	76	71	80	74	70	77	73	69	75	71	67	65			65
4	87	76	68	62	84	74	67	61	72	66	61	70	64	60	68	63	59	57			57
5	80	68	60	54	78	67	59	54	65	58	53	63	57	53	61	56	52	50			50
6	74	62	54	48	72	61	53	47	59	52	47	58	51	47	56	51	46	44			44
7	69	56	48	42	67	56	48	42	54	47	42	53	46	42	51	46	41	40			40
8	64	52	44	38	63	51	43	38	50	43	38	48	42	38	47	42	37	36			36
9	60	48	40	35	59	47	40	34	46	39	34	45	39	34	44	38	34	32			32
10	57	44	36	31	55	43	36	31	43	36	31	42	35	31	41	35	31	29			29

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P205053

CATALOG NUMBER: LD6B70D010TE EU6B60708030 6LBCSMMS1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	315.5	4.3
10°-20°	885.2	12.1
20°-30°	1293.0	17.7
30°-40°	1478.8	20.3
40°-50°	1421.3	19.5
50°-60°	1097.5	15.1
60°-70°	612.5	8.4
70°-80°	178.3	2.4
80°-90°	7.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2493.7	34.2
0°-40°	3972.5	54.5
0°-60°	6491.2	89.0
0°-90°	7289.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7289.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3348	
5°	3319	315
15°	3140	885
25°	2810	1293
35°	2367	1479
45°	1853	1421
55°	1231	1097
65°	613	613
75°	156	178
85°	5	8
90°	0	



TEST NUMBER: P205053

CATALOG NUMBER: LD6B70D010TE EU6B60708030 6LBCSMMS1

CANDELA DISTRIBUTION (FULL):

	0°
0°	3347.6
2.5°	3347.6
5°	3319.3
7.5°	3305.2
10°	3258.0
12.5°	3201.5
15°	3140.2
17.5°	3078.9
20°	2989.3
22.5°	2918.6
25°	2810.1
27.5°	2701.7
30°	2593.2
32.5°	2484.8
35°	2366.9
37.5°	2249.0
40°	2112.3
42.5°	1989.7
45°	1853.0
47.5°	1697.4
50°	1551.2
52.5°	1390.9
55°	1230.6
57.5°	1065.6
60°	910.0
62.5°	754.4
65°	612.9
67.5°	480.9
70°	358.3
72.5°	249.9
75°	155.6
77.5°	80.2
80°	28.3
82.5°	9.4
85°	4.7
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)