

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P684001

Luminaire Tested: **LX6C130D010 EX6C1309030 6LBWH**

Issue Date: 2/15/2022



Test Information

Test Method: LM-79-08
Report Number: P684001
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P202739)
Test Lab: INNOVATION CENTER
Issue Date: 2/15/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX6C130D010 EX6C1309030 6LBWH
Description: 6 INCH 13000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS
AND 6LBW TRIM WITH H FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 12061.0 lumens
Efficiency: N/A
Efficacy: 83.6 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.16
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 144.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P684001

CATALOG NUMBER: LX6C130D010 EX6C1309030 6LBWH

Luminous Intensity Polar Plot





TEST NUMBER: P684001

CATALOG NUMBER: LX6C130D010 EX6C1309030 6LBWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	103	110	107	104	101	103	100	98	99	97	95	95	94	93	91			91
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81			81
3	98	90	84	79	96	89	83	78	86	81	77	83	79	76	81	78	75	73			73
4	92	82	75	70	90	81	75	70	79	73	69	77	72	68	75	71	67	65			65
5	86	75	68	63	84	74	68	63	72	66	62	71	65	61	69	64	61	59			59
6	80	69	62	57	78	68	61	56	67	61	56	65	60	56	64	59	55	53			53
7	75	64	56	51	73	63	56	51	62	55	51	60	55	51	59	54	50	49			49
8	70	59	52	47	69	58	51	47	57	51	46	56	50	46	55	50	46	44			44
9	66	55	48	43	65	54	47	43	53	47	43	52	47	42	51	46	42	41			41
10	62	51	44	40	61	50	44	39	50	43	39	49	43	39	48	43	39	38			38

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	407796
5°	407654
10°	404518
15°	401807
20°	395686
25°	386647
30°	364050
35°	329462
40°	275115
45°	210805
50°	149300
55°	94123
60°	53099
65°	34465
70°	22504
75°	16542
80°	9944
85°	9875



TEST NUMBER: P684001

CATALOG NUMBER: LX6C130D010 EX6C1309030 6LBWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	702.6	5.8
10°-20°	1993.6	16.5
20°-30°	2923.1	24.2
30°-40°	3042.2	25.2
40°-50°	2104.8	17.5
50°-60°	916.5	7.6
60°-70°	281.1	2.3
70°-80°	84.2	0.7
80°-90°	12.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5619.4	46.6
0°-40°	8661.6	71.8
0°-60°	11682.9	96.9
0°-90°	12061.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	12061.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7439	
5°	7408	703
15°	7080	1994
25°	6392	2923
35°	4923	3042
45°	2719	2105
55°	985	916
65°	266	281
75°	78	84
85°	16	13
90°	0	



TEST NUMBER: P684001

CATALOG NUMBER: LX6C130D010 EX6C1309030 6LBWH

CANDELA DISTRIBUTION (FULL):

	0°
0°	7438.8
2.5°	7454.5
5°	7407.9
7.5°	7345.5
10°	7266.9
12.5°	7188.8
15°	7079.8
17.5°	6938.8
20°	6782.6
22.5°	6610.7
25°	6392.2
27.5°	6110.7
30°	5751.1
32.5°	5375.9
35°	4923.0
37.5°	4423.0
40°	3844.4
42.5°	3266.3
45°	2719.1
47.5°	2203.4
50°	1750.6
52.5°	1328.7
55°	984.8
57.5°	703.4
60°	484.3
62.5°	359.6
65°	265.7
67.5°	203.4
70°	140.4
72.5°	109.6
75°	78.1
77.5°	46.6
80°	31.5
82.5°	15.7
85°	15.7
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)