

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P684830

Luminaire Tested: **LX6C130D010 EX61309035 6LRMDLI**

Issue Date: 2/15/2022



**Test Information**

Test Method: LM-79-08  
Report Number: P684830  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-20)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/15/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LX6C130D010 EX61309035 6LRMDLI  
Description: 6 INCH 13000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3500K, 90CRI LEDS  
AND 6LRMD45 TRIM WITH LI FINISH  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 10374.0 lumens  
Efficiency: N/A  
Efficacy: 71.9 lumens/watt  
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.77  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 144.3  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P684830

CATALOG NUMBER: LX6C130D010 EX61309035 6LRMDLI

### Luminous Intensity Polar Plot





TEST NUMBER: P684830

CATALOG NUMBER: LX6C130D010 EX61309035 6LRMDLI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94			
2	109	104	101	97	107	103	99	96	99	97	94	96	94	92	94	92	90	89			
3	104	98	93	90	102	97	92	89	94	90	87	92	89	86	89	87	85	83			
4	99	92	87	83	97	91	86	83	89	85	82	87	83	81	85	82	80	78			
5	95	87	81	77	93	86	81	77	84	80	76	83	79	76	81	78	75	74			
6	90	82	77	73	89	81	76	72	80	75	72	79	74	71	77	74	71	70			
7	86	78	72	68	85	77	72	68	76	71	68	75	70	67	74	70	67	66			
8	83	74	68	64	81	73	68	64	72	67	64	71	67	64	70	66	63	62			
9	79	70	65	61	78	70	64	61	69	64	61	68	63	60	67	63	60	59			
10	76	67	61	58	75	66	61	58	65	61	57	65	60	57	64	60	57	56			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	849428
5°	851060
10°	811063
15°	698375
20°	575322
25°	449361
30°	324531
35°	166197
40°	81045
45°	33670
50°	6132
55°	3565
60°	2335
65°	1725
70°	1282
75°	1123
80°	852
85°	0



TEST NUMBER: P684830

CATALOG NUMBER: LX6C130D010 EX61309035 6LRMDLI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	1449.6	14.0
10°-20°	3410.6	32.9
20°-30°	3377.9	32.6
30°-40°	1712.4	16.5
40°-50°	368.9	3.6
50°-60°	35.1	0.3
60°-70°	13.5	0.1
70°-80°	4.9	0.0
80°-90°	1.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	8238.1	79.4
0°-40°	9950.5	95.9
0°-60°	10354.5	99.8
0°-90°	10374.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	10374.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	15495	
5°	15466	###
15°	12305	3411
25°	7429	3378
35°	2483	1712
45°	434	369
55°	37	35
65°	13	13
75°	5	5
85°	0	1
90°	0	



TEST NUMBER: P684830

CATALOG NUMBER: LX6C130D010 EX61309035 6LRMDLI

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	15494.8
2.5°	15513.5
5°	15465.5
7.5°	15223.1
10°	14570.2
12.5°	13520.4
15°	12305.3
17.5°	11060.9
20°	9861.8
22.5°	8662.7
25°	7429.0
27.5°	6171.3
30°	5126.8
32.5°	3949.0
35°	2483.4
37.5°	1670.7
40°	1132.5
42.5°	732.8
45°	434.3
47.5°	194.5
50°	71.9
52.5°	48.0
55°	37.3
57.5°	26.6
60°	21.3
62.5°	16.0
65°	13.3
67.5°	10.7
70°	8.0
72.5°	5.3
75°	5.3
77.5°	2.7
80°	2.7
82.5°	2.7
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)