

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P202580

Luminaire Tested: **LD6B70D010TE EU6B60708030 6LBSWMH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P202580
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B70D010TE EU6B60708030 6LBSWMH1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH WARM HAZE TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7448.6 lumens
Efficiency: N/A
Efficacy: 93.8 lumens/watt
Spacing Criteria (0/90/45): 0.97 / 0.97 / 1.1
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 79.45
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P202580

CATALOG NUMBER: LD6B70D010TE EU6B60708030 6LBSWMH1

Luminous Intensity Polar Plot





TEST NUMBER: P202580

CATALOG NUMBER: LD6B70D010TE EU6B60708030 6LBSWMH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	88				88
2	103	96	90	85	100	94	89	84	91	86	82	87	84	81	84	81	79	77				77
3	95	86	79	73	92	84	78	73	81	76	71	79	74	70	76	72	69	67				67
4	88	77	70	64	86	76	69	63	74	67	62	71	66	62	69	65	61	59				59
5	81	70	62	56	79	69	61	56	67	60	55	65	59	55	63	58	54	52				52
6	76	64	56	50	74	63	55	50	61	54	49	59	53	49	58	53	48	47				47
7	70	58	50	45	69	57	50	45	56	49	44	55	48	44	53	48	44	42				42
8	66	54	46	40	64	53	45	40	52	45	40	50	44	40	49	44	40	38				38
9	62	49	42	37	61	49	42	37	48	41	37	47	41	36	46	40	36	35				35
10	58	46	39	34	57	45	38	34	45	38	34	44	38	33	43	37	33	32				32

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P202580

CATALOG NUMBER: LD6B70D010TE EU6B60708030 6LBSWMH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	398.5	5.4
10°-20°	1041.7	14.0
20°-30°	1381.3	18.5
30°-40°	1473.3	19.8
40°-50°	1377.3	18.5
50°-60°	1050.1	14.1
60°-70°	571.2	7.7
70°-80°	153.2	2.1
80°-90°	1.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2821.6	37.9
0°-40°	4294.9	57.7
0°-60°	6722.3	90.2
0°-90°	7448.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7448.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4307	
5°	4248	399
15°	3714	1042
25°	3007	1381
35°	2354	1473
45°	1793	1377
55°	1182	1050
65°	570	571
75°	132	153
85°	0	2
90°	0	



TEST NUMBER: P202580

CATALOG NUMBER: LD6B70D010TE EU6B60708030 6LBSWMH1

CANDELA DISTRIBUTION (FULL):

0°	
0°	4307.3
2.5°	4293.6
5°	4248.0
7.5°	4152.1
10°	4042.6
12.5°	3887.5
15°	3714.1
17.5°	3540.7
20°	3353.7
22.5°	3175.7
25°	3006.9
27.5°	2828.9
30°	2660.1
32.5°	2495.8
35°	2354.4
37.5°	2213.0
40°	2066.9
42.5°	1934.6
45°	1793.2
47.5°	1638.0
50°	1492.0
52.5°	1336.9
55°	1181.8
57.5°	1012.9
60°	857.8
62.5°	711.8
65°	570.3
67.5°	442.6
70°	324.0
72.5°	223.6
75°	132.3
77.5°	59.3
80°	13.7
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)