

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P684008

Luminaire Tested: **LX6C130D010 EX6C1309035 6LBSQH**

Issue Date: 2/16/2022

Test Information

Test Method: LM-79-08
Report Number: P684008
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P203254)
Test Lab: INNOVATION CENTER
Issue Date: 2/16/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX6C130D010 EX6C1309035 6LBSQH
Description: 6 INCH 13000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3500K, 90CRI LEDS
AND 6LBSQ TRIM WITH H FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8488.0 lumens
Efficiency: N/A
Efficacy: 58.8 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.93
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 144.3
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P684008

CATALOG NUMBER: LX6C130D010 EX6C1309035 6LBSQH

Luminous Intensity Polar Plot





TEST NUMBER: P684008

CATALOG NUMBER: LX6C130D010 EX6C1309035 6LBSQH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	92			92
2	107	102	97	93	105	100	96	92	97	93	90	94	91	88	91	89	87	85			85
3	101	94	88	84	99	92	87	84	90	86	82	87	84	81	85	82	80	78			78
4	95	87	81	76	93	86	80	76	84	79	75	82	78	74	80	76	73	72			72
5	90	81	75	70	88	80	74	70	78	73	69	76	72	68	75	71	68	66			66
6	85	75	69	64	83	75	69	64	73	68	64	72	67	63	70	66	63	61			61
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57			57
8	76	66	60	55	75	65	59	55	64	59	55	63	58	55	62	58	54	53			53
9	72	62	56	51	71	61	55	51	60	55	51	60	55	51	59	54	51	49			49
10	69	58	52	48	68	58	52	48	57	52	48	56	51	48	55	51	48	46			46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	361676
5°	355200
10°	337050
15°	316064
20°	294354
25°	271216
30°	225986
35°	159276
40°	101512
45°	60537
50°	35729
55°	22730
60°	15655
65°	11115
70°	7654
75°	6055
80°	2975
85°	0



TEST NUMBER: P684008

CATALOG NUMBER: LX6C130D010 EX6C1309035 6LBSQH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	768.1	9.0
10°-20°	1986.9	23.4
20°-30°	2574.5	30.3
30°-40°	1911.4	22.5
40°-50°	806.9	9.5
50°-60°	286.5	3.4
60°-70°	110.6	1.3
70°-80°	38.3	0.5
80°-90°	4.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5329.5	62.8
0°-40°	7240.9	85.3
0°-60°	8334.2	98.2
0°-90°	8488.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8488.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8400	
5°	8218	768
15°	7091	1987
25°	5709	2575
35°	3030	1911
45°	994	807
55°	303	286
65°	109	111
75°	36	38
85°	0	5
90°	0	



TEST NUMBER: P684008

CATALOG NUMBER: LX6C130D010 EX6C1309035 6LBSQH

CANDELA DISTRIBUTION (FULL):

	0°
0°	8400.2
2.5°	8375.8
5°	8218.4
7.5°	7987.8
10°	7709.3
12.5°	7406.0
15°	7090.7
17.5°	6739.6
20°	6424.3
22.5°	6097.1
25°	5709.0
27.5°	5175.6
30°	4545.5
32.5°	3805.9
35°	3030.3
37.5°	2375.9
40°	1806.1
42.5°	1345.3
45°	994.2
47.5°	727.2
50°	533.4
52.5°	400.0
55°	302.8
57.5°	230.1
60°	181.8
62.5°	133.5
65°	109.1
67.5°	84.7
70°	60.8
72.5°	48.3
75°	36.4
77.5°	24.4
80°	12.0
82.5°	12.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)