

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P202998

Luminaire Tested: **LD6B70D010TE EU6B60709030 6LBWGPH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P202998
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B70D010TE EU6B60709030 6LBWGPH1
Description: PORTFOLIO 6 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTIONWITH GRAPHITE HAZE TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4029.3 lumens
Efficiency: N/A
Efficacy: 50.7 lumens/watt
Spacing Criteria (0/90/45): 1.11 / 1.11 / 1.11
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 79.45
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P202998

CATALOG NUMBER: LD6B70D010TE EU6B60709030 6LBWGP1

Luminous Intensity Polar Plot





TEST NUMBER: P202998

CATALOG NUMBER: LD6B70D010TE EU6B60709030 6LBWGPH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	86	84	82			
3	99	91	85	81	97	90	84	80	87	82	79	85	81	77	82	79	76	74			
4	93	84	77	72	91	82	76	72	80	75	71	78	74	70	76	72	69	67			
5	87	77	70	65	85	76	69	65	74	68	64	72	67	63	71	66	63	61			
6	81	71	64	59	80	70	63	59	68	62	58	67	62	58	65	61	57	56			
7	76	65	58	53	75	65	58	53	63	57	53	62	57	53	61	56	52	51			
8	72	61	54	49	70	60	53	49	59	53	49	58	52	48	57	52	48	47			
9	68	57	50	45	66	56	49	45	55	49	45	54	48	45	53	48	44	43			
10	64	53	46	42	63	52	46	42	51	45	41	51	45	41	50	45	41	40			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P202998

CATALOG NUMBER: LD6B70D010TE EU6B60709030 6LBWGPH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	258.0	6.4
10°-20°	723.4	18.0
20°-30°	1035.0	25.7
30°-40°	1031.7	25.6
40°-50°	657.1	16.3
50°-60°	242.3	6.0
60°-70°	60.6	1.5
70°-80°	18.3	0.5
80°-90°	2.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2016.5	50.0
0°-40°	3048.2	75.7
0°-60°	3947.6	98.0
0°-90°	4029.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4029.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2738	
5°	2725	258
15°	2572	723
25°	2260	1035
35°	1678	1032
45°	846	657
55°	256	242
65°	56	61
75°	14	18
85°	0	3
90°	0	



TEST NUMBER: P202998

CATALOG NUMBER: LD6B70D010TE EU6B60709030 6LBWGPH1

CANDELA DISTRIBUTION (FULL):

0°	
0°	2738.5
2.5°	2738.5
5°	2724.6
7.5°	2696.9
10°	2662.2
12.5°	2620.6
15°	2572.1
17.5°	2509.7
20°	2440.4
22.5°	2364.1
25°	2260.1
27.5°	2149.2
30°	2003.6
32.5°	1851.1
35°	1677.8
37.5°	1469.8
40°	1254.9
42.5°	1046.9
45°	845.8
47.5°	665.6
50°	499.2
52.5°	367.4
55°	256.5
57.5°	166.4
60°	110.9
62.5°	76.3
65°	55.5
67.5°	41.6
70°	34.7
72.5°	20.8
75°	13.9
77.5°	13.9
80°	6.9
82.5°	6.9
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)