

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P205573

Luminaire Tested: **LD6B70D010TE EU6B60709730 6LBMGPH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P205573
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B70D010TE EU6B60709730 6LBMGPH1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH GRAPHITE HAZE TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2952.1 lumens
Efficiency: N/A
Efficacy: 37.2 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.91
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 79.45
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P205573

CATALOG NUMBER: LD6B70D010TE EU6B60709730 6LBMGPH1

Luminous Intensity Polar Plot





TEST NUMBER: P205573

CATALOG NUMBER: LD6B70D010TE EU6B60709730 6LBMGPH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	108	105	111	108	106	104	104	102	101	100	99	98	97	96	95	93				93
2	107	102	98	94	105	100	97	93	97	94	91	94	92	89	91	89	87	86				86
3	102	95	90	85	100	93	89	85	91	87	83	88	85	82	86	83	81	79				79
4	96	88	82	78	94	87	82	77	85	80	77	83	79	76	81	78	75	73				73
5	91	82	76	72	89	81	76	71	79	74	71	78	73	70	76	72	69	68				68
6	86	77	71	66	85	76	70	66	74	69	65	73	68	65	72	68	64	63				63
7	82	72	66	61	80	71	65	61	70	65	61	69	64	60	68	63	60	59				59
8	77	68	61	57	76	67	61	57	66	60	57	65	60	56	64	59	56	55				55
9	74	64	57	53	72	63	57	53	62	57	53	61	56	53	60	56	53	51				51
10	70	60	54	50	69	59	54	50	59	53	50	58	53	49	57	53	49	48				48

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P205573

CATALOG NUMBER: LD6B70D010TE EU6B60709730 6LBMGPH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	282.6	9.6
10°-20°	733.3	24.8
20°-30°	934.3	31.6
30°-40°	660.3	22.4
40°-50°	241.1	8.2
50°-60°	66.8	2.3
60°-70°	24.2	0.8
70°-80°	8.7	0.3
80°-90°	0.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1950.3	66.1
0°-40°	2610.6	88.4
0°-60°	2918.5	98.9
0°-90°	2952.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2952.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3076	
5°	3023	283
15°	2611	733
25°	2075	934
35°	1049	660
45°	292	241
55°	72	67
65°	24	24
75°	6	9
85°	0	1
90°	0	



TEST NUMBER: P205573

CATALOG NUMBER: LD6B70D010TE EU6B60709730 6LBMGPH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	3076.3
2.5°	3064.4
5°	3022.6
7.5°	2939.2
10°	2849.7
12.5°	2730.5
15°	2611.3
17.5°	2492.0
20°	2372.8
22.5°	2229.7
25°	2074.7
27.5°	1860.1
30°	1621.6
32.5°	1335.4
35°	1049.3
37.5°	798.9
40°	584.3
42.5°	423.3
45°	292.1
47.5°	196.7
50°	131.2
52.5°	89.4
55°	71.5
57.5°	53.7
60°	41.7
62.5°	29.8
65°	23.8
67.5°	17.9
70°	11.9
72.5°	11.9
75°	6.0
77.5°	6.0
80°	6.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)