

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P684015

Luminaire Tested: **LX6C130D010 EX6C1309040 6LBSH**

Issue Date: 2/15/2022



Test Information

Test Method: LM-79-08
Report Number: P684015
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P204188)
Test Lab: INNOVATION CENTER
Issue Date: 2/15/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX6C130D010 EX6C1309040 6LBSH
Description: 6 INCH 13000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 4000K, 90CRI LEDS
AND 6LBS TRIM WITH H FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 14421.1 lumens
Efficiency: N/A
Efficacy: 99.9 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 144.3
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P684015

CATALOG NUMBER: LX6C130D010 EX6C1309040 6LBSH

Luminous Intensity Polar Plot





TEST NUMBER: P684015

CATALOG NUMBER: LX6C130D010 EX6C1309040 6LBSH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|---|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | | 0 | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | |
| 1 | 111 | 107 | 104 | 101 | 108 | 105 | 102 | 99 | 101 | 98 | 96 | 97 | 95 | 93 | 93 | 92 | 90 | 88 | | | |
| 2 | 102 | 96 | 90 | 85 | 100 | 94 | 88 | 84 | 90 | 86 | 82 | 87 | 83 | 80 | 84 | 81 | 79 | 77 | | | |
| 3 | 95 | 85 | 78 | 73 | 92 | 84 | 77 | 72 | 81 | 75 | 71 | 78 | 74 | 70 | 76 | 72 | 69 | 67 | | | |
| 4 | 87 | 77 | 69 | 63 | 85 | 75 | 68 | 63 | 73 | 67 | 62 | 71 | 65 | 61 | 69 | 64 | 60 | 58 | | | |
| 5 | 81 | 69 | 61 | 55 | 79 | 68 | 61 | 55 | 66 | 60 | 55 | 64 | 59 | 54 | 63 | 58 | 53 | 51 | | | |
| 6 | 75 | 63 | 55 | 49 | 73 | 62 | 54 | 49 | 60 | 54 | 49 | 59 | 53 | 48 | 57 | 52 | 48 | 46 | | | |
| 7 | 70 | 58 | 50 | 44 | 68 | 57 | 49 | 44 | 55 | 49 | 44 | 54 | 48 | 43 | 53 | 47 | 43 | 41 | | | |
| 8 | 65 | 53 | 45 | 40 | 64 | 52 | 45 | 40 | 51 | 44 | 39 | 50 | 44 | 39 | 49 | 43 | 39 | 37 | | | |
| 9 | 61 | 49 | 41 | 36 | 60 | 48 | 41 | 36 | 47 | 40 | 36 | 46 | 40 | 36 | 45 | 40 | 35 | 34 | | | |
| 10 | 58 | 45 | 38 | 33 | 56 | 45 | 38 | 33 | 44 | 37 | 33 | 43 | 37 | 33 | 42 | 37 | 33 | 31 | | | |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|--------|
| | 0° |
| 0° | 413465 |
| 5° | 411533 |
| 10° | 403043 |
| 15° | 388385 |
| 20° | 370525 |
| 25° | 350555 |
| 30° | 330671 |
| 35° | 311353 |
| 40° | 293164 |
| 45° | 273276 |
| 50° | 249177 |
| 55° | 220064 |
| 60° | 186268 |
| 65° | 146254 |
| 70° | 104361 |
| 75° | 57167 |
| 80° | 10071 |
| 85° | 0 |



TEST NUMBER: P684015

CATALOG NUMBER: LX6C130D010 EX6C1309040 6LBSH

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|---------|-----------|
| 0°-10° | 706.4 | 4.9 |
| 10°-20° | 1920.1 | 13.3 |
| 20°-30° | 2666.6 | 18.5 |
| 30°-40° | 2909.9 | 20.2 |
| 40°-50° | 2714.5 | 18.8 |
| 50°-60° | 2060.4 | 14.3 |
| 60°-70° | 1128.2 | 7.8 |
| 70°-80° | 310.5 | 2.2 |
| 80°-90° | 4.3 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 5293.2 | 36.7 |
| 0°-40° | 8203.1 | 56.9 |
| 0°-60° | 12978.1 | 90.0 |
| 0°-90° | 14421.1 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 14421.1 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 7542 | |
| 5° | 7478 | 706 |
| 15° | 6843 | 1920 |
| 25° | 5796 | 2667 |
| 35° | 4652 | 2910 |
| 45° | 3525 | 2715 |
| 55° | 2302 | 2060 |
| 65° | 1128 | 1128 |
| 75° | 270 | 310 |
| 85° | 0 | 4 |
| 90° | 0 | |



TEST NUMBER: P684015

CATALOG NUMBER: LX6C130D010 EX6C1309040 6LBSH

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|--------|
| 0° | 7542.2 |
| 2.5° | 7542.2 |
| 5° | 7478.4 |
| 7.5° | 7383.2 |
| 10° | 7240.4 |
| 12.5° | 7049.8 |
| 15° | 6843.3 |
| 17.5° | 6589.3 |
| 20° | 6351.3 |
| 22.5° | 6065.4 |
| 25° | 5795.5 |
| 27.5° | 5525.6 |
| 30° | 5223.8 |
| 32.5° | 4937.9 |
| 35° | 4652.4 |
| 37.5° | 4366.6 |
| 40° | 4096.6 |
| 42.5° | 3810.8 |
| 45° | 3524.9 |
| 47.5° | 3239.1 |
| 50° | 2921.7 |
| 52.5° | 2619.9 |
| 55° | 2302.5 |
| 57.5° | 2000.7 |
| 60° | 1698.9 |
| 62.5° | 1397.4 |
| 65° | 1127.5 |
| 67.5° | 873.2 |
| 70° | 651.1 |
| 72.5° | 444.6 |
| 75° | 269.9 |
| 77.5° | 127.2 |
| 80° | 31.9 |
| 82.5° | 0.0 |
| 85° | 0.0 |
| 87.5° | 0.0 |
| 90° | 0.0 |



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)