

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P684840

Luminaire Tested: **LX6C130D010 EX61309050 6LRMDLI**

Issue Date: 2/15/2022

**Test Information**

Test Method: LM-79-08  
Report Number: P684840  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-20)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/15/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LX6C130D010 EX61309050 6LRMDLI  
Description: 6 INCH 13000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 5000K, 90CRI LEDS  
AND 6LRMD45 TRIM WITH LI FINISH  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 10602.9 lumens  
Efficiency: N/A  
Efficacy: 73.5 lumens/watt  
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.77  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 144.3  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P684840

CATALOG NUMBER: LX6C130D010 EX61309050 6LRMDLI

### Luminous Intensity Polar Plot





TEST NUMBER: P684840

CATALOG NUMBER: LX6C130D010 EX61309050 6LRMDLI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94			
2	109	104	101	97	107	103	99	96	99	97	94	96	94	92	94	92	90	89			
3	104	98	93	90	102	97	92	89	94	90	87	92	89	86	89	87	85	83			
4	99	92	87	83	97	91	86	83	89	85	82	87	83	81	85	82	80	78			
5	95	87	81	77	93	86	81	77	84	80	76	83	79	76	81	78	75	74			
6	90	82	77	73	89	81	76	72	80	75	72	79	74	71	77	74	71	70			
7	86	78	72	68	85	77	72	68	76	71	68	75	71	67	74	70	67	66			
8	83	74	68	64	81	73	68	64	72	67	64	71	67	64	70	66	63	62			
9	79	70	65	61	78	70	64	61	69	64	61	68	63	60	67	63	60	59			
10	76	67	61	58	75	66	61	58	65	61	57	65	60	57	64	60	57	56			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	868182
5°	869847
10°	828965
15°	713790
20°	588022
25°	459281
30°	331690
35°	169871
40°	82834
45°	34414
50°	6268
55°	3641
60°	2390
65°	1764
70°	1314
75°	1144
80°	852
85°	0



TEST NUMBER: P684840

CATALOG NUMBER: LX6C130D010 EX61309050 6LRMDLI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	1481.6	14.0
10°-20°	3485.9	32.9
20°-30°	3452.5	32.6
30°-40°	1750.2	16.5
40°-50°	377.0	3.6
50°-60°	35.9	0.3
60°-70°	13.8	0.1
70°-80°	5.0	0.0
80°-90°	1.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	8419.9	79.4
0°-40°	10170.1	95.9
0°-60°	10583.1	99.8
0°-90°	10602.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	10602.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	15837	
5°	15807	###
15°	12577	3486
25°	7593	3452
35°	2538	1750
45°	444	377
55°	38	36
65°	14	14
75°	5	5
85°	0	1
90°	0	



TEST NUMBER: P684840

CATALOG NUMBER: LX6C130D010 EX61309050 6LRMDLI

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	15836.9
2.5°	15856.0
5°	15806.9
7.5°	15559.1
10°	14891.8
12.5°	13818.8
15°	12576.9
17.5°	11305.1
20°	10079.5
22.5°	8854.0
25°	7593.0
27.5°	6307.5
30°	5239.9
32.5°	4036.2
35°	2538.3
37.5°	1707.6
40°	1157.5
42.5°	748.9
45°	443.9
47.5°	198.8
50°	73.5
52.5°	49.0
55°	38.1
57.5°	27.2
60°	21.8
62.5°	16.3
65°	13.6
67.5°	10.9
70°	8.2
72.5°	5.4
75°	5.4
77.5°	2.7
80°	2.7
82.5°	2.7
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)