

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203199

Luminaire Tested: **LD6B70D010TE EU6B60708035 6LBWMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203199
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B70D010TE EU6B60708035 6LBWMW1
Description: PORTFOLIO 6 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTION WITH MATTE WHITE TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6871.0 lumens
Efficiency: N/A
Efficacy: 86.5 lumens/watt
Spacing Criteria (0/90/45): 1.13 / 1.13 / 1.15
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 79.45
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203199

CATALOG NUMBER: LD6B70D010TE EU6B60708035 6LBWMW1

Luminous Intensity Polar Plot





TEST NUMBER: P203199

CATALOG NUMBER: LD6B70D010TE EU6B60708035 6LBWMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	100	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	103	96	90	86	100	94	89	85	91	86	83	88	84	81	85	82	79	77			
3	95	86	80	74	93	85	79	74	82	77	72	80	75	71	77	73	70	68			
4	89	78	71	65	86	77	70	65	75	69	64	72	67	63	70	66	62	60			
5	82	71	64	58	80	70	63	58	68	62	57	66	61	56	65	60	56	54			
6	77	65	57	52	75	64	57	52	63	56	51	61	55	51	60	54	50	49			
7	72	60	52	47	70	59	52	47	58	51	46	56	50	46	55	50	46	44			
8	67	55	48	42	66	55	47	42	53	47	42	52	46	42	51	46	42	40			
9	63	51	44	39	62	51	44	39	50	43	39	49	43	38	48	42	38	37			
10	60	48	40	36	58	47	40	36	46	40	36	45	40	35	45	39	35	34			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203199

CATALOG NUMBER: LD6B70D010TE EU6B60708035 6LBWMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	363.4	5.3
10°-20°	1019.1	14.8
20°-30°	1468.3	21.4
30°-40°	1524.5	22.2
40°-50°	1127.1	16.4
50°-60°	673.2	9.8
60°-70°	409.1	6.0
70°-80°	224.1	3.3
80°-90°	62.3	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2850.7	41.5
0°-40°	4375.2	63.7
0°-60°	6175.5	89.9
0°-90°	6871.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6871.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3858	
5°	3834	363
15°	3617	1019
25°	3200	1468
35°	2458	1524
45°	1450	1127
55°	733	673
65°	408	409
75°	208	224
85°	50	62
90°	0	



TEST NUMBER: P203199

CATALOG NUMBER: LD6B70D010TE EU6B60708035 6LBWMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	3858.5
2.5°	3858.5
5°	3833.5
7.5°	3800.2
10°	3750.2
12.5°	3691.8
15°	3616.8
17.5°	3533.5
20°	3450.2
22.5°	3333.5
25°	3200.2
27.5°	3058.5
30°	2875.1
32.5°	2691.8
35°	2458.5
37.5°	2216.8
40°	1950.1
42.5°	1691.7
45°	1450.1
47.5°	1233.4
50°	1041.7
52.5°	875.0
55°	733.4
57.5°	625.0
60°	533.4
62.5°	466.7
65°	408.4
67.5°	358.4
70°	308.3
72.5°	258.3
75°	208.3
77.5°	166.7
80°	125.0
82.5°	91.7
85°	50.0
87.5°	25.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)