

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204855

Luminaire Tested: **LD6B70D010TE EU6B60709035 6LBCSMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204855
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B70D010TE EU6B60709035 6LBCSMW1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH CAST MATTE WHITE TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6743.7 lumens
Efficiency: N/A
Efficacy: 84.9 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct

Input Watts (W): 79.45
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204855
CATALOG NUMBER: LD6B70D010TE EU6B60709035 6LBCSMW1

Luminous Intensity Polar Plot





TEST NUMBER: P204855

CATALOG NUMBER: LD6B70D010TE EU6B60709035 6LBCSMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	110	106	102	99	108	104	100	97	100	97	94	96	93	91	92	90	89	87																			
2	101	94	87	82	99	92	86	81	88	84	79	85	81	78	82	79	76	74																			
3	93	83	75	70	90	81	74	69	79	73	68	76	71	67	73	69	65	63																			
4	85	74	66	60	83	73	65	59	70	64	58	68	62	58	66	61	57	55																			
5	79	66	58	52	77	65	57	51	63	56	51	61	55	50	60	54	50	48																			
6	73	60	52	45	71	59	51	45	57	50	45	56	49	44	54	49	44	42																			
7	68	55	46	40	66	54	46	40	52	45	40	51	44	40	50	44	39	37																			
8	63	50	42	36	61	49	41	36	48	41	36	47	40	36	46	40	35	33																			
9	59	46	38	33	57	45	38	32	44	37	32	43	37	32	42	36	32	30																			
10	55	42	35	30	54	42	34	30	41	34	29	40	34	29	39	33	29	27																			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204855

CATALOG NUMBER: LD6B70D010TE EU6B60709035 6LBCSMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	261.0	3.9
10°-20°	742.9	11.0
20°-30°	1117.6	16.6
30°-40°	1324.5	19.6
40°-50°	1318.1	19.5
50°-60°	1062.6	15.8
60°-70°	642.8	9.5
70°-80°	238.7	3.5
80°-90°	35.6	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2121.5	31.5
0°-40°	3446.0	51.1
0°-60°	5826.6	86.4
0°-90°	6743.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6743.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2754	
5°	2742	261
15°	2632	743
25°	2427	1118
35°	2121	1324
45°	1716	1318
55°	1185	1063
65°	646	643
75°	217	239
85°	29	36
90°	0	



TEST NUMBER: P204855

CATALOG NUMBER: LD6B70D010TE EU6B60709035 6LBCSMW1

CANDELA DISTRIBUTION (FULL):

0°	
0°	2754.3
2.5°	2754.3
5°	2742.1
7.5°	2733.9
10°	2709.4
12.5°	2668.5
15°	2631.7
17.5°	2590.9
20°	2541.8
22.5°	2492.8
25°	2427.4
27.5°	2357.9
30°	2280.3
32.5°	2206.7
35°	2120.9
37.5°	2031.0
40°	1924.8
42.5°	1822.6
45°	1716.3
47.5°	1597.8
50°	1467.1
52.5°	1332.2
55°	1185.1
57.5°	1054.3
60°	907.2
62.5°	776.4
65°	645.7
67.5°	523.1
70°	408.7
72.5°	306.5
75°	216.6
77.5°	138.9
80°	81.7
82.5°	49.0
85°	28.6
87.5°	12.3
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)