

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P202587

Luminaire Tested: **LD6B70D010TE EU6B60709035 6LBSWMH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P202587
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B70D010TE EU6B60709035 6LBSWMH1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH WARM HAZE TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6452.5 lumens
Efficiency: N/A
Efficacy: 81.2 lumens/watt
Spacing Criteria (0/90/45): 0.97 / 0.97 / 1.1
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 79.45
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P202587

CATALOG NUMBER: LD6B70D010TE EU6B60709035 6LBSWMH1

Luminous Intensity Polar Plot





TEST NUMBER: P202587

CATALOG NUMBER: LD6B70D010TE EU6B60709035 6LBSWMH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	88			
2	103	96	90	85	100	94	89	84	91	86	82	87	84	81	84	81	79	77			
3	95	86	79	73	92	84	78	73	81	76	71	79	74	70	76	72	69	67			
4	88	77	70	64	86	76	69	63	74	67	62	71	66	62	69	65	61	59			
5	81	70	62	56	79	69	61	56	67	60	55	65	59	55	63	58	54	52			
6	76	64	56	50	74	63	55	50	61	54	49	59	53	49	58	53	48	47			
7	70	58	50	45	69	57	50	45	56	49	44	55	48	44	53	48	44	42			
8	66	54	46	40	64	53	45	40	52	45	40	50	44	40	49	44	40	38			
9	62	49	42	37	61	49	42	37	48	41	37	47	41	36	46	40	36	35			
10	58	46	39	34	57	45	38	34	45	38	34	44	38	33	43	37	33	32			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P202587

CATALOG NUMBER: LD6B70D010TE EU6B60709035 6LBSWMH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	345.2	5.4
10°-20°	902.4	14.0
20°-30°	1196.6	18.5
30°-40°	1276.3	19.8
40°-50°	1193.1	18.5
50°-60°	909.7	14.1
60°-70°	494.9	7.7
70°-80°	132.7	2.1
80°-90°	1.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2444.2	37.9
0°-40°	3720.5	57.7
0°-60°	5823.3	90.2
0°-90°	6452.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6452.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3731	
5°	3680	345
15°	3217	902
25°	2605	1197
35°	2040	1276
45°	1553	1193
55°	1024	910
65°	494	495
75°	115	133
85°	0	2
90°	0	



TEST NUMBER: P202587

CATALOG NUMBER: LD6B70D010TE EU6B60709035 6LBSWMH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	3731.2
2.5°	3719.4
5°	3679.8
7.5°	3596.8
10°	3502.0
12.5°	3367.6
15°	3217.4
17.5°	3067.2
20°	2905.1
22.5°	2751.0
25°	2604.7
27.5°	2450.6
30°	2304.3
32.5°	2162.0
35°	2039.5
37.5°	1917.0
40°	1790.5
42.5°	1675.9
45°	1553.4
47.5°	1419.0
50°	1292.5
52.5°	1158.1
55°	1023.7
57.5°	877.5
60°	743.1
62.5°	616.6
65°	494.1
67.5°	383.4
70°	280.6
72.5°	193.7
75°	114.6
77.5°	51.4
80°	11.9
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)