

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P205564

Luminaire Tested: **LD6B70D010TE EU6B60708040 6LBMGPH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P205564
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B70D010TE EU6B60708040 6LBMGPH1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH GRAPHITE HAZE TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4096.4 lumens
Efficiency: N/A
Efficacy: 51.6 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.91
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 79.45
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P205564

CATALOG NUMBER: LD6B70D010TE EU6B60708040 6LBMGPH1

Luminous Intensity Polar Plot





TEST NUMBER: P205564

CATALOG NUMBER: LD6B70D010TE EU6B60708040 6LBMGPH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0										
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100							100												
1	113	110	108	105	111	108	106	104	104	102	101	100	99	98	97	96	95	93							93												
2	107	102	98	94	105	100	97	93	97	94	91	94	92	89	91	89	87	86							86												
3	102	95	90	85	100	93	89	85	91	87	83	88	85	82	86	83	81	79							79												
4	96	88	82	78	94	87	82	77	85	80	77	83	79	76	81	78	75	73							73												
5	91	82	76	72	89	81	76	71	79	74	71	78	73	70	76	72	69	68							68												
6	86	77	71	66	85	76	70	66	74	69	65	73	68	65	72	68	64	63							63												
7	82	72	66	61	80	71	65	61	70	65	61	69	64	60	68	63	60	59							59												
8	77	68	61	57	76	67	61	57	66	60	57	65	60	56	64	59	56	55							55												
9	74	64	57	53	72	63	57	53	62	57	53	61	56	53	60	56	53	51							51												
10	70	60	54	50	69	59	54	50	59	53	50	58	53	49	57	53	49	48							48												

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P205564

CATALOG NUMBER: LD6B70D010TE EU6B60708040 6LBMGPH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	392.1	9.6
10°-20°	1017.6	24.8
20°-30°	1296.5	31.6
30°-40°	916.3	22.4
40°-50°	334.5	8.2
50°-60°	92.7	2.3
60°-70°	33.6	0.8
70°-80°	12.0	0.3
80°-90°	1.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2706.2	66.1
0°-40°	3622.4	88.4
0°-60°	4049.7	98.9
0°-90°	4096.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4096.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4269	
5°	4194	392
15°	3623	1018
25°	2879	1296
35°	1456	916
45°	405	335
55°	99	93
65°	33	34
75°	8	12
85°	0	1
90°	0	



TEST NUMBER: P205564

CATALOG NUMBER: LD6B70D010TE EU6B60708040 6LBMGPH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	4268.6
2.5°	4252.1
5°	4194.2
7.5°	4078.4
10°	3954.3
12.5°	3788.8
15°	3623.4
17.5°	3457.9
20°	3292.5
22.5°	3093.9
25°	2878.8
27.5°	2581.0
30°	2250.1
32.5°	1853.1
35°	1456.0
37.5°	1108.5
40°	810.7
42.5°	587.4
45°	405.4
47.5°	273.0
50°	182.0
52.5°	124.1
55°	99.3
57.5°	74.5
60°	57.9
62.5°	41.4
65°	33.1
67.5°	24.8
70°	16.5
72.5°	16.5
75°	8.3
77.5°	8.3
80°	8.3
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)