

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P684852

Luminaire Tested: **LX6C15D010 EX6159030 6LBSLI**

Issue Date: 2/15/2022

Test Information

Test Method: LM-79-08
Report Number: P684852
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205419)
Test Lab: INNOVATION CENTER
Issue Date: 2/15/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX6C15D010 EX6159030 6LBSLI
Description: 6 INCH 1500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS
AND 6LBS TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1702.0 lumens
Efficiency: N/A
Efficacy: 107.7 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 1.04
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P684852
CATALOG NUMBER: LX6C15D010 EX6159030 6LBSLI

Luminous Intensity Polar Plot





TEST NUMBER: P684852

CATALOG NUMBER: LX6C15D010 EX6159030 6LBSLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	109	105	102	99	101	99	96	97	95	93	94	92	91	89			
2	103	96	91	86	100	94	89	85	91	87	83	88	84	81	85	82	79	77			
3	95	86	79	74	93	85	78	73	82	76	72	79	75	71	77	73	70	68			
4	88	78	70	64	86	77	69	64	74	68	63	72	67	62	70	65	62	60			
5	82	71	63	57	80	70	62	57	67	61	56	66	60	55	64	59	55	53			
6	76	64	56	51	74	63	56	51	62	55	50	60	54	50	59	53	49	47			
7	71	59	51	46	70	58	51	45	57	50	45	55	49	45	54	49	45	43			
8	67	54	47	41	65	54	46	41	52	46	41	51	45	41	50	45	41	39			
9	63	50	43	38	61	50	43	38	49	42	38	48	42	37	47	41	37	36			
10	59	47	40	35	58	46	39	35	45	39	35	45	39	34	44	38	34	33			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	58877
5°	58210
10°	55259
15°	50999
20°	46624
25°	42220
30°	38455
35°	35576
40°	33255
45°	30980
50°	28221
55°	24716
60°	20612
65°	16189
70°	11300
75°	6121
80°	1137
85°	0



TEST NUMBER: P684852

CATALOG NUMBER: LX6C15D010 EX6159030 6LBSLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	99.0	5.8
10°-20°	252.0	14.8
20°-30°	321.3	18.9
30°-40°	333.2	19.6
40°-50°	307.0	18.0
50°-60°	230.9	13.6
60°-70°	124.7	7.3
70°-80°	33.4	2.0
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	672.2	39.5
0°-40°	1005.4	59.1
0°-60°	1543.4	90.7
0°-90°	1702.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1702.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1074	
5°	1058	99
15°	899	252
25°	698	321
35°	532	333
45°	400	307
55°	259	231
65°	125	125
75°	29	33
85°	0	0
90°	0	



TEST NUMBER: P684852

CATALOG NUMBER: LX6C15D010 EX6159030 6LBSLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	1074.0
2.5°	1070.4
5°	1057.8
7.5°	1034.3
10°	992.7
12.5°	951.1
15°	898.6
17.5°	849.9
20°	799.2
22.5°	746.8
25°	698.0
27.5°	651.0
30°	607.5
32.5°	567.8
35°	531.6
37.5°	497.2
40°	464.7
42.5°	430.4
45°	399.6
47.5°	365.3
50°	330.9
52.5°	294.7
55°	258.6
57.5°	222.4
60°	188.0
62.5°	155.5
65°	124.8
67.5°	95.8
70°	70.5
72.5°	48.8
75°	28.9
77.5°	12.6
80°	3.6
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)