

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203303

Luminaire Tested: **LD6B70D010TE EU6B60708040 6LBMH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203303
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B70D010TE EU6B60708040 6LBMH1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5366.5 lumens
Efficiency: N/A
Efficacy: 67.5 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.93
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 79.45
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203303

CATALOG NUMBER: LD6B70D010TE EU6B60708040 6LBMH1

Luminous Intensity Polar Plot





TEST NUMBER: P203303

CATALOG NUMBER: LD6B70D010TE EU6B60708040 6LBMH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	92		
2	107	102	97	93	105	100	96	92	97	93	90	94	91	88	91	89	87	85		
3	101	94	88	84	99	92	87	84	90	86	82	87	84	81	85	82	80	78		
4	95	87	81	76	93	86	80	76	84	79	75	82	78	74	80	76	73	72		
5	90	81	75	70	88	80	74	70	78	73	69	76	72	68	75	71	68	66		
6	85	75	69	64	83	75	69	64	73	68	64	72	67	63	70	66	63	61		
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57		
8	76	66	60	55	75	65	59	55	64	59	55	63	58	55	62	58	54	53		
9	72	62	56	51	71	61	55	51	60	55	51	60	55	51	59	54	51	49		
10	69	58	52	48	68	58	52	48	57	52	48	56	51	48	55	51	48	46		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203303

CATALOG NUMBER: LD6B70D010TE EU6B60708040 6LBMH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	485.6	9.0
10°-20°	1256.2	23.4
20°-30°	1627.7	30.3
30°-40°	1208.4	22.5
40°-50°	510.1	9.5
50°-60°	181.2	3.4
60°-70°	69.9	1.3
70°-80°	24.2	0.5
80°-90°	3.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3369.5	62.8
0°-40°	4577.9	85.3
0°-60°	5269.2	98.2
0°-90°	5366.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5366.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5311	
5°	5196	486
15°	4483	1256
25°	3610	1628
35°	1916	1208
45°	628	510
55°	192	181
65°	69	70
75°	23	24
85°	0	3
90°	0	



TEST NUMBER: P203303

CATALOG NUMBER: LD6B70D010TE EU6B60708040 6LBMH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	5310.8
2.5°	5295.5
5°	5195.8
7.5°	5050.2
10°	4874.0
12.5°	4682.4
15°	4483.1
17.5°	4260.9
20°	4061.6
22.5°	3854.7
25°	3609.5
27.5°	3272.3
30°	2873.8
32.5°	2406.3
35°	1915.9
37.5°	1502.0
40°	1141.9
42.5°	850.6
45°	628.4
47.5°	459.8
50°	337.2
52.5°	252.9
55°	191.6
57.5°	145.6
60°	115.0
62.5°	84.3
65°	69.0
67.5°	53.6
70°	38.3
72.5°	30.7
75°	23.0
77.5°	15.3
80°	7.7
82.5°	7.7
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)