

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203715

Luminaire Tested: **LD6B70D010TE EU6B60708040 6LBNH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203715
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B70D010TE EU6B60708040 6LBNH1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
NARROW DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4617.9 lumens
Efficiency: N/A
Efficacy: 58.1 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.84
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 79.45
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203715

CATALOG NUMBER: LD6B70D010TE EU6B60708040 6LBNH1

Luminous Intensity Polar Plot





TEST NUMBER: P203715

CATALOG NUMBER: LD6B70D010TE EU6B60708040 6LBNH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	111	108	106	111	109	106	104	104	103	101	101	99	98	97	96	95	93																			
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87																			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81																			
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	83	79	77	75																			
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70																			
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	65																			
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61																			
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58																			
9	76	66	60	56	75	66	60	56	65	59	56	64	59	56	63	59	55	54																			
10	72	62	57	53	71	62	57	53	61	56	53	60	56	52	60	55	52	51																			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203715

CATALOG NUMBER: LD6B70D010TE EU6B60708040 6LBNH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	532.3	11.5
10°-20°	1269.5	27.5
20°-30°	1454.3	31.5
30°-40°	977.2	21.2
40°-50°	279.2	6.0
50°-60°	68.3	1.5
60°-70°	25.9	0.6
70°-80°	10.0	0.2
80°-90°	1.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3256.2	70.5
0°-40°	4233.3	91.7
0°-60°	4580.8	99.2
0°-90°	4617.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4617.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5920	
5°	5751	532
15°	4556	1269
25°	3175	1454
35°	1558	977
45°	320	279
55°	76	68
65°	25	26
75°	8	10
85°	0	1
90°	0	



TEST NUMBER: P203715

CATALOG NUMBER: LD6B70D010TE EU6B60708040 6LBNH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	5919.7
2.5°	5877.6
5°	5751.2
7.5°	5523.9
10°	5246.0
12.5°	4892.3
15°	4555.5
17.5°	4201.9
20°	3848.2
22.5°	3511.4
25°	3174.6
27.5°	2863.0
30°	2500.9
32.5°	2020.9
35°	1557.8
37.5°	1136.8
40°	783.1
42.5°	513.7
45°	320.0
47.5°	193.7
50°	117.9
52.5°	92.6
55°	75.8
57.5°	58.9
60°	42.1
62.5°	33.7
65°	25.3
67.5°	16.8
70°	16.8
72.5°	8.4
75°	8.4
77.5°	8.4
80°	8.4
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)