

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P684060

Luminaire Tested: **LX6C15D010 EX6C159035 6LBNH**

Issue Date: 2/15/2022



Test Information

Test Method: LM-79-08
Report Number: P684060
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P203666)
Test Lab: INNOVATION CENTER
Issue Date: 2/15/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX6C15D010 EX6C159035 6LBNH
Description: 6 INCH 1500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3500K, 90CRI LEDS
AND 6LBN TRIM WITH H FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1007.0 lumens
Efficiency: N/A
Efficacy: 63.7 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.84
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P684060

CATALOG NUMBER: LX6C15D010 EX6C159035 6LBNH

Luminous Intensity Polar Plot





TEST NUMBER: P684060

CATALOG NUMBER: LX6C15D010 EX6C159035 6LBNH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	93		
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87		
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81		
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	83	79	77	75		
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70		
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	65		
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61		
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58		
9	76	66	60	56	75	66	60	56	65	59	56	64	59	56	63	59	55	54		
10	72	62	57	53	71	62	57	53	61	56	53	60	56	52	60	55	52	51		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	70767
5°	69013
10°	63682
15°	56379
20°	48952
25°	41869
30°	34518
35°	22734
40°	12223
45°	5411
50°	2192
55°	1587
60°	1009
65°	713
70°	593
75°	381
80°	568
85°	0



TEST NUMBER: P684060

CATALOG NUMBER: LX6C15D010 EX6C159035 6LBNH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	116.1	11.5
10°-20°	276.8	27.5
20°-30°	317.1	31.5
30°-40°	213.1	21.2
40°-50°	60.9	6.0
50°-60°	14.9	1.5
60°-70°	5.7	0.6
70°-80°	2.2	0.2
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	710.0	70.5
0°-40°	923.1	91.7
0°-60°	998.9	99.2
0°-90°	1007.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1007.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1291	
5°	1254	116
15°	993	277
25°	692	317
35°	340	213
45°	70	61
55°	17	15
65°	6	6
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P684060

CATALOG NUMBER: LX6C15D010 EX6C159035 6LBNH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1290.9
2.5°	1281.7
5°	1254.1
7.5°	1204.5
10°	1144.0
12.5°	1066.8
15°	993.4
17.5°	916.3
20°	839.1
22.5°	765.7
25°	692.2
27.5°	624.3
30°	545.3
32.5°	440.7
35°	339.7
37.5°	247.9
40°	170.8
42.5°	112.0
45°	69.8
47.5°	42.2
50°	25.7
52.5°	20.2
55°	16.6
57.5°	12.9
60°	9.2
62.5°	7.3
65°	5.5
67.5°	3.7
70°	3.7
72.5°	1.8
75°	1.8
77.5°	1.8
80°	1.8
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)