

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204856

Luminaire Tested: **LD6B70D010TE EU6B60709040 6LBCSMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204856
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B70D010TE EU6B60709040 6LBCSMW1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH CAST MATTE WHITE TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6755.0 lumens
Efficiency: N/A
Efficacy: 85.0 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 79.45
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204856

CATALOG NUMBER: LD6B70D010TE EU6B60709040 6LBCSMW1

Luminous Intensity Polar Plot





TEST NUMBER: P204856

CATALOG NUMBER: LD6B70D010TE EU6B60709040 6LBSCMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	110	106	102	99	108	104	100	97	100	97	94	96	93	91	92	90	89	87			87
2	101	94	87	82	99	92	86	81	88	84	79	85	81	78	82	79	76	74			74
3	93	83	75	70	90	81	74	69	79	73	68	76	71	67	73	69	65	63			63
4	85	74	66	60	83	73	65	59	70	64	58	68	62	58	66	61	57	55			55
5	79	66	58	52	77	65	57	51	63	56	51	61	55	50	60	54	50	48			48
6	73	60	52	45	71	59	51	45	57	50	45	56	49	44	54	49	44	42			42
7	68	55	46	40	66	54	46	40	52	45	40	51	44	40	50	44	39	37			37
8	63	50	42	36	61	49	41	36	48	41	36	47	40	36	46	40	35	33			33
9	59	46	38	33	57	45	38	32	44	37	32	43	37	32	42	36	32	30			30
10	55	42	35	30	54	42	34	30	41	34	29	40	34	29	39	33	29	27			27

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204856

CATALOG NUMBER: LD6B70D010TE EU6B60709040 6LBCSMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	261.4	3.9
10°-20°	744.2	11.0
20°-30°	1119.5	16.6
30°-40°	1326.7	19.6
40°-50°	1320.3	19.5
50°-60°	1064.4	15.8
60°-70°	643.9	9.5
70°-80°	239.1	3.5
80°-90°	35.6	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2125.1	31.5
0°-40°	3451.8	51.1
0°-60°	5836.4	86.4
0°-90°	6755.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6755.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2759	
5°	2747	261
15°	2636	744
25°	2432	1119
35°	2124	1327
45°	1719	1320
55°	1187	1064
65°	647	644
75°	217	239
85°	29	36
90°	0	



TEST NUMBER: P204856

CATALOG NUMBER: LD6B70D010TE EU6B60709040 6LBCSMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	2759.0
2.5°	2759.0
5°	2746.7
7.5°	2738.5
10°	2713.9
12.5°	2673.0
15°	2636.2
17.5°	2595.2
20°	2546.1
22.5°	2497.0
25°	2431.5
27.5°	2361.9
30°	2284.1
32.5°	2210.4
35°	2124.5
37.5°	2034.4
40°	1928.0
42.5°	1825.7
45°	1719.2
47.5°	1600.5
50°	1469.5
52.5°	1334.5
55°	1187.1
57.5°	1056.1
60°	908.7
62.5°	777.7
65°	646.8
67.5°	524.0
70°	409.3
72.5°	307.0
75°	217.0
77.5°	139.2
80°	81.9
82.5°	49.1
85°	28.7
87.5°	12.3
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)