

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P684875

Luminaire Tested: **LX6C15D010 EX6159050 6LRMDLI**

Issue Date: 2/15/2022



Test Information

Test Method: LM-79-08
Report Number: P684875
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-20)
Test Lab: INNOVATION CENTER
Issue Date: 2/15/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX6C15D010 EX6159050 6LRMDLI
Description: 6 INCH 1500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 5000K, 90CRI LEDS
AND 6LRMD45 TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1228.0 lumens
Efficiency: N/A
Efficacy: 77.7 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.77
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P684875

CATALOG NUMBER: LX6C15D010 EX6159050 6LRMDLI

Luminous Intensity Polar Plot





TEST NUMBER: P684875

CATALOG NUMBER: LX6C15D010 EX6159050 6LRMDLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | | 0 | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | 100 | 100 | 100 |
| 1 | 114 | 111 | 109 | 107 | 111 | 109 | 107 | 105 | 105 | 103 | 102 | 101 | 100 | 99 | 98 | 97 | 96 | 94 | 94 | 94 | 94 |
| 2 | 109 | 104 | 101 | 97 | 107 | 103 | 99 | 96 | 99 | 97 | 94 | 96 | 94 | 92 | 94 | 92 | 90 | 89 | 89 | 89 | 89 |
| 3 | 104 | 98 | 93 | 90 | 102 | 97 | 92 | 89 | 94 | 90 | 87 | 92 | 89 | 86 | 89 | 87 | 85 | 83 | 83 | 83 | 83 |
| 4 | 99 | 92 | 87 | 83 | 97 | 91 | 86 | 83 | 89 | 85 | 82 | 87 | 83 | 81 | 85 | 82 | 80 | 78 | 78 | 78 | 78 |
| 5 | 95 | 87 | 81 | 77 | 93 | 86 | 81 | 77 | 84 | 80 | 76 | 83 | 79 | 76 | 81 | 78 | 75 | 74 | 74 | 74 | 74 |
| 6 | 90 | 82 | 77 | 73 | 89 | 81 | 76 | 72 | 80 | 75 | 72 | 79 | 74 | 71 | 77 | 74 | 71 | 70 | 70 | 70 | 70 |
| 7 | 86 | 78 | 72 | 68 | 85 | 77 | 72 | 68 | 76 | 71 | 68 | 75 | 71 | 67 | 74 | 70 | 67 | 66 | 66 | 66 | 66 |
| 8 | 83 | 74 | 68 | 64 | 81 | 73 | 68 | 64 | 72 | 67 | 64 | 71 | 67 | 64 | 70 | 66 | 63 | 62 | 62 | 62 | 62 |
| 9 | 79 | 70 | 65 | 61 | 78 | 70 | 64 | 61 | 69 | 64 | 61 | 68 | 63 | 60 | 67 | 63 | 60 | 59 | 59 | 59 | 59 |
| 10 | 76 | 67 | 61 | 58 | 75 | 66 | 61 | 58 | 65 | 61 | 57 | 65 | 60 | 57 | 64 | 60 | 57 | 56 | 56 | 56 | 56 |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|--------|
| | 0° |
| 0° | 100551 |
| 5° | 100743 |
| 10° | 96007 |
| 15° | 82668 |
| 20° | 68104 |
| 25° | 53193 |
| 30° | 38417 |
| 35° | 19675 |
| 40° | 9597 |
| 45° | 3985 |
| 50° | 725 |
| 55° | 421 |
| 60° | 274 |
| 65° | 208 |
| 70° | 144 |
| 75° | 127 |
| 80° | 95 |
| 85° | 0 |



TEST NUMBER: P684875

CATALOG NUMBER: LX6C15D010 EX6159050 6LRMDLI

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 171.6 | 14.0 |
| 10°-20° | 403.7 | 32.9 |
| 20°-30° | 399.9 | 32.6 |
| 30°-40° | 202.7 | 16.5 |
| 40°-50° | 43.7 | 3.6 |
| 50°-60° | 4.2 | 0.3 |
| 60°-70° | 1.6 | 0.1 |
| 70°-80° | 0.6 | 0.0 |
| 80°-90° | 0.1 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 975.2 | 79.4 |
| 0°-40° | 1177.9 | 95.9 |
| 0°-60° | 1225.7 | 99.8 |
| 0°-90° | 1228.0 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 1228.0 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 1834 | |
| 5° | 1831 | 172 |
| 15° | 1457 | 404 |
| 25° | 879 | 400 |
| 35° | 294 | 203 |
| 45° | 51 | 44 |
| 55° | 4 | 4 |
| 65° | 2 | 2 |
| 75° | 1 | 1 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P684875

CATALOG NUMBER: LX6C15D010 EX6159050 6LRMDLI

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|--------|
| 0° | 1834.2 |
| 2.5° | 1836.4 |
| 5° | 1830.7 |
| 7.5° | 1802.0 |
| 10° | 1724.7 |
| 12.5° | 1600.4 |
| 15° | 1456.6 |
| 17.5° | 1309.3 |
| 20° | 1167.4 |
| 22.5° | 1025.4 |
| 25° | 879.4 |
| 27.5° | 730.5 |
| 30° | 606.9 |
| 32.5° | 467.5 |
| 35° | 294.0 |
| 37.5° | 197.8 |
| 40° | 134.1 |
| 42.5° | 86.7 |
| 45° | 51.4 |
| 47.5° | 23.0 |
| 50° | 8.5 |
| 52.5° | 5.7 |
| 55° | 4.4 |
| 57.5° | 3.2 |
| 60° | 2.5 |
| 62.5° | 1.9 |
| 65° | 1.6 |
| 67.5° | 1.3 |
| 70° | 0.9 |
| 72.5° | 0.6 |
| 75° | 0.6 |
| 77.5° | 0.3 |
| 80° | 0.3 |
| 82.5° | 0.3 |
| 85° | 0.0 |
| 87.5° | 0.0 |
| 90° | 0.0 |



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)