

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P205364

Luminaire Tested: **LD6B70D010TE EU6B60709040 6LBNLI1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P205364  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD6B70D010TE EU6B60709040 6LBNLI1  
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT  
NARROW DISTRIBUTION WITH SPECULAR CLEAR TRIM  
SINGLE DRIVER D010TE  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4890.2 lumens  
Efficiency: N/A  
Efficacy: 61.6 lumens/watt  
Spacing Criteria (0/90/45): 0.53 / 0.53 / 0.58  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 79.45  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P205364

CATALOG NUMBER: LD6B70D010TE EU6B60709040 6LBNLI1

### Luminous Intensity Polar Plot





TEST NUMBER: P205364

CATALOG NUMBER: LD6B70D010TE EU6B60709040 6LBNL11

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	112	109	107	112	109	107	106	105	104	102	102	101	99	98	97	96	95			
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	89			
3	105	99	94	91	103	97	93	90	95	91	89	93	90	87	90	88	86	85			
4	100	93	88	85	98	92	88	84	90	86	83	88	85	82	86	84	81	80			
5	96	88	83	79	94	87	83	79	86	82	78	84	81	78	83	80	77	76			
6	92	84	79	75	90	83	78	75	82	77	74	80	76	74	79	76	73	72			
7	88	80	74	71	87	79	74	71	78	73	70	77	73	70	76	72	69	68			
8	84	76	71	67	83	75	70	67	74	70	67	73	69	66	73	69	66	65			
9	81	73	67	64	80	72	67	64	71	67	63	70	66	63	70	66	63	62			
10	78	69	64	61	77	69	64	61	68	64	61	67	63	60	67	63	60	59			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P205364

CATALOG NUMBER: LD6B70D010TE EU6B60709040 6LBNLI1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	925.7	18.9
10°-20°	1661.5	34.0
20°-30°	1343.4	27.5
30°-40°	773.9	15.8
40°-50°	163.6	3.3
50°-60°	14.1	0.3
60°-70°	7.0	0.1
70°-80°	0.9	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3930.6	80.4
0°-40°	4704.5	96.2
0°-60°	4882.2	99.8
0°-90°	4890.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4890.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	11134	
5°	10372	926
15°	6036	1662
25°	2898	1343
35°	1227	774
45°	176	164
55°	14	14
65°	7	7
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P205364

CATALOG NUMBER: LD6B70D010TE EU6B60709040 6LBNLI1

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	11133.7
2.5°	10999.7
5°	10372.2
7.5°	9469.6
10°	8362.6
12.5°	7227.4
15°	6035.8
17.5°	4886.4
20°	4047.3
22.5°	3405.7
25°	2898.0
27.5°	2467.9
30°	2080.1
32.5°	1650.0
35°	1226.9
37.5°	853.2
40°	557.0
42.5°	338.5
45°	176.3
47.5°	70.5
50°	21.2
52.5°	21.2
55°	14.1
57.5°	14.1
60°	7.1
62.5°	7.1
65°	7.1
67.5°	7.1
70°	7.1
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)