

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203819

Luminaire Tested: **LD6B70D010TE EU6B60708050 6LBNWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203819
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B70D010TE EU6B60708050 6LBNWH1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
NARROW DISTRIBUTION WITH WHEAT TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4943.1 lumens
Efficiency: N/A
Efficacy: 62.2 lumens/watt
Spacing Criteria (0/90/45): 0.56 / 0.56 / 0.64
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 79.45
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203819

CATALOG NUMBER: LD6B70D010TE EU6B60708050 6LBNWH1

Luminous Intensity Polar Plot





TEST NUMBER: P203819

CATALOG NUMBER: LD6B70D010TE EU6B60708050 6LBNWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	109	107	112	109	107	105	105	104	102	101	100	99	98	97	96	94			
2	109	104	101	97	107	103	99	96	99	97	94	96	94	92	94	92	90	89			
3	104	98	93	90	102	97	92	89	94	91	88	92	89	86	89	87	85	83			
4	99	92	87	83	97	91	86	83	89	85	82	87	84	81	85	82	80	79			
5	95	87	82	78	93	86	81	77	84	80	77	83	79	76	81	78	75	74			
6	91	82	77	73	89	82	76	73	80	76	72	79	75	72	78	74	71	70			
7	87	78	73	69	85	77	72	69	76	72	68	75	71	68	74	70	67	66			
8	83	74	69	65	82	74	68	65	73	68	65	72	67	64	71	67	64	63			
9	79	71	65	62	78	70	65	61	69	65	61	68	64	61	68	64	61	60			
10	76	67	62	58	75	67	62	58	66	61	58	65	61	58	65	61	58	57			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203819

CATALOG NUMBER: LD6B70D010TE EU6B60708050 6LBNWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	821.5	16.6
10°-20°	1578.6	31.9
20°-30°	1435.1	29.0
30°-40°	869.9	17.6
40°-50°	198.1	4.0
50°-60°	25.2	0.5
60°-70°	11.4	0.2
70°-80°	3.3	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3835.2	77.6
0°-40°	4705.1	95.2
0°-60°	4928.4	99.7
0°-90°	4943.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4943.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	9705	
5°	9150	822
15°	5685	1579
25°	3112	1435
35°	1379	870
45°	219	198
55°	25	25
65°	8	11
75°	0	3
85°	0	0
90°	0	



TEST NUMBER: P203819

CATALOG NUMBER: LD6B70D010TE EU6B60708050 6LBNWH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	9704.9
2.5°	9587.2
5°	9149.8
7.5°	8443.4
10°	7543.6
12.5°	6610.1
15°	5685.0
17.5°	4844.0
20°	4137.6
22.5°	3565.7
25°	3111.6
27.5°	2707.9
30°	2312.7
32.5°	1850.2
35°	1379.2
37.5°	967.1
40°	639.1
42.5°	395.3
45°	218.7
47.5°	100.9
50°	42.0
52.5°	33.6
55°	25.2
57.5°	25.2
60°	16.8
62.5°	16.8
65°	8.4
67.5°	8.4
70°	8.4
72.5°	8.4
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)