

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P684890

Luminaire Tested: **LX6C20D010 EX6209027 6LRMDLI**

Issue Date: 2/15/2022



Test Information

Test Method: LM-79-08
Report Number: P684890
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-20)
Test Lab: INNOVATION CENTER
Issue Date: 2/15/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX6C20D010 EX6209027 6LRMDLI
Description: 6 INCH 2000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 2700K, 90CRI LEDS
AND 6LRMD45 TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1470.0 lumens
Efficiency: N/A
Efficacy: 67.4 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.77
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 21.8
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P684890

CATALOG NUMBER: LX6C20D010 EX6209027 6LRMDLI

Luminous Intensity Polar Plot





TEST NUMBER: P684890

CATALOG NUMBER: LX6C20D010 EX6209027 6LRMDLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94			
2	109	104	100	97	107	103	99	96	99	97	94	96	94	92	94	92	90	89			
3	104	98	93	90	102	97	92	89	94	90	87	92	89	86	89	87	85	83			
4	99	92	87	83	97	91	86	83	89	85	82	87	83	81	85	82	80	78			
5	95	87	81	77	93	86	81	77	84	80	76	83	79	76	81	78	75	74			
6	90	82	77	73	89	81	76	72	80	75	72	79	74	71	77	74	71	70			
7	86	78	72	68	85	77	72	68	76	71	68	75	70	67	74	70	67	66			
8	83	74	68	64	81	73	68	64	72	67	64	71	67	64	70	66	63	62			
9	79	70	65	61	78	70	64	61	69	64	61	68	63	60	67	63	60	59			
10	76	67	61	58	75	66	61	58	65	61	57	65	60	57	64	60	57	56			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	120363
5°	120597
10°	114928
15°	98962
20°	81522
25°	63675
30°	45988
35°	23550
40°	11486
45°	4768
50°	870
55°	507
60°	329
65°	246
70°	176
75°	169
80°	126
85°	0



TEST NUMBER: P684890

CATALOG NUMBER: LX6C20D010 EX6209027 6LRMDLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	205.4	14.0
10°-20°	483.3	32.9
20°-30°	478.7	32.6
30°-40°	242.6	16.5
40°-50°	52.3	3.6
50°-60°	5.0	0.3
60°-70°	1.9	0.1
70°-80°	0.7	0.0
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1167.3	79.4
0°-40°	1410.0	95.9
0°-60°	1467.2	99.8
0°-90°	1470.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1470.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2196	
5°	2192	205
15°	1744	483
25°	1053	479
35°	352	243
45°	62	52
55°	5	5
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P684890

CATALOG NUMBER: LX6C20D010 EX6209027 6LRMDLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	2195.6
2.5°	2198.3
5°	2191.5
7.5°	2157.1
10°	2064.6
12.5°	1915.8
15°	1743.7
17.5°	1567.3
20°	1397.4
22.5°	1227.5
25°	1052.7
27.5°	874.5
30°	726.5
32.5°	559.6
35°	351.9
37.5°	236.7
40°	160.5
42.5°	103.8
45°	61.5
47.5°	27.6
50°	10.2
52.5°	6.8
55°	5.3
57.5°	3.8
60°	3.0
62.5°	2.3
65°	1.9
67.5°	1.5
70°	1.1
72.5°	0.8
75°	0.8
77.5°	0.4
80°	0.4
82.5°	0.4
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)