

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203825

Luminaire Tested: **LD6B70D010TE EU6B60709050 6LBNWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203825
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B70D010TE EU6B60709050 6LBNWH1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
NARROW DISTRIBUTION WITH WHEAT TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4161.3 lumens
Efficiency: N/A
Efficacy: 52.4 lumens/watt
Spacing Criteria (0/90/45): 0.56 / 0.56 / 0.64
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 79.45
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203825

CATALOG NUMBER: LD6B70D010TE EU6B60709050 6LBNWH1

Luminous Intensity Polar Plot





TEST NUMBER: P203825

CATALOG NUMBER: LD6B70D010TE EU6B60709050 6LBNWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	109	107	112	109	107	105	105	104	102	101	100	99	98	97	96	94			
2	109	104	101	97	107	103	99	96	99	97	94	96	94	92	94	92	90	89			
3	104	98	93	90	102	97	92	89	94	91	88	92	89	86	89	87	85	83			
4	99	92	87	83	97	91	86	83	89	85	82	87	84	81	85	82	80	79			
5	95	87	82	78	93	86	81	77	84	80	77	83	79	76	81	78	75	74			
6	91	82	77	73	89	82	76	73	80	76	72	79	75	72	78	74	71	70			
7	87	78	73	69	85	77	72	69	76	72	68	75	71	68	74	70	67	66			
8	83	74	69	65	82	74	68	65	73	68	65	72	67	64	71	67	64	63			
9	79	71	65	62	78	70	65	61	69	65	61	68	64	61	68	64	61	60			
10	76	67	62	58	75	67	62	58	66	61	58	65	61	58	65	61	58	57			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203825

CATALOG NUMBER: LD6B70D010TE EU6B60709050 6LBNWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	691.6	16.6
10°-20°	1328.9	31.9
20°-30°	1208.1	29.0
30°-40°	732.3	17.6
40°-50°	166.7	4.0
50°-60°	21.3	0.5
60°-70°	9.6	0.2
70°-80°	2.8	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3228.6	77.6
0°-40°	3960.9	95.2
0°-60°	4148.8	99.7
0°-90°	4161.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4161.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8170	
5°	7703	692
15°	4786	1329
25°	2619	1208
35°	1161	732
45°	184	167
55°	21	21
65°	7	10
75°	0	3
85°	0	0
90°	0	



TEST NUMBER: P203825

CATALOG NUMBER: LD6B70D010TE EU6B60709050 6LBNWH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	8169.8
2.5°	8070.7
5°	7702.6
7.5°	7107.9
10°	6350.4
12.5°	5564.5
15°	4785.8
17.5°	4077.8
20°	3483.1
22.5°	3001.7
25°	2619.4
27.5°	2279.6
30°	1946.9
32.5°	1557.5
35°	1161.0
37.5°	814.1
40°	538.0
42.5°	332.7
45°	184.1
47.5°	85.0
50°	35.4
52.5°	28.3
55°	21.2
57.5°	21.2
60°	14.2
62.5°	14.2
65°	7.1
67.5°	7.1
70°	7.1
72.5°	7.1
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)