

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P684109

Luminaire Tested: **LX6C20D010 EX6C209035 6LBNH**

Issue Date: 2/15/2022

**Test Information**

Test Method: LM-79-08  
Report Number: P684109  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P203666)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/15/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LX6C20D010 EX6C209035 6LBNH  
Description: 6 INCH 2000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3500K, 90CRI LEDS  
AND 6LBN TRIM WITH H FINISH  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1299.0 lumens  
Efficiency: N/A  
Efficacy: 59.6 lumens/watt  
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.84  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 21.8  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P684109

CATALOG NUMBER: LX6C20D010 EX6C209035 6LBNH

### Luminous Intensity Polar Plot





TEST NUMBER: P684109

CATALOG NUMBER: LX6C20D010 EX6C209035 6LBNH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	109	106	104	104	103	101	101	99	98	97	96	95	93			
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	83	79	77	75			
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70			
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	65			
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61			
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58			
9	76	66	60	56	75	66	60	56	65	59	56	64	59	56	63	59	55	54			
10	72	62	57	53	71	62	57	53	61	56	53	60	56	52	60	55	52	51			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	91287
5°	89027
10°	82146
15°	72730
20°	63145
25°	54015
30°	44532
35°	29326
40°	15765
45°	6977
50°	2831
55°	2045
60°	1294
65°	921
70°	769
75°	508
80°	758
85°	0



TEST NUMBER: P684109

CATALOG NUMBER: LX6C20D010 EX6C209035 6LBNH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	149.7	11.5
10°-20°	357.1	27.5
20°-30°	409.1	31.5
30°-40°	274.8	21.2
40°-50°	78.5	6.0
50°-60°	19.2	1.5
60°-70°	7.3	0.6
70°-80°	2.9	0.2
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	915.9	70.5
0°-40°	1190.8	91.7
0°-60°	1288.5	99.2
0°-90°	1299.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1299.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1665	
5°	1618	150
15°	1282	357
25°	893	409
35°	438	275
45°	90	79
55°	21	19
65°	7	7
75°	2	3
85°	0	0
90°	0	



TEST NUMBER: P684109

CATALOG NUMBER: LX6C20D010 EX6C209035 6LBNH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1665.2
2.5°	1653.4
5°	1617.8
7.5°	1553.8
10°	1475.7
12.5°	1376.2
15°	1281.5
17.5°	1182.0
20°	1082.4
22.5°	987.7
25°	893.0
27.5°	805.3
30°	703.5
32.5°	568.4
35°	438.2
37.5°	319.7
40°	220.3
42.5°	144.5
45°	90.0
47.5°	54.5
50°	33.2
52.5°	26.0
55°	21.4
57.5°	16.6
60°	11.8
62.5°	9.4
65°	7.1
67.5°	4.8
70°	4.8
72.5°	2.4
75°	2.4
77.5°	2.4
80°	2.4
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)