

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P582957

Luminaire Tested: **LX6C20D010 EU6209050 6LBHYLI**

Issue Date: 8/31/2023

**Test Information**

Test Method: LM-79-08  
Report Number: P582957  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2301-896-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 8/31/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LX6C20D010 EU6209050 6LBHYLI  
Description: 6 INCH 2000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 5000K, 90CRI LEDS  
AND 6LCHYP TRIM WITH LI FINISH  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1390.9 lumens  
Efficiency: N/A  
Efficacy: 63.8 lumens/watt  
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.52  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 21.8  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P582957

CATALOG NUMBER: LX6C20D010 EU6209050 6LBHYLI

### Luminous Intensity Polar Plot





TEST NUMBER: P582957

CATALOG NUMBER: LX6C20D010 EU6209050 6LBHYLI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96			
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92			
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89			
4	103	98	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85			
5	100	94	89	86	98	93	89	86	91	87	85	89	86	84	88	85	83	82			
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79			
7	93	87	82	79	92	86	82	79	85	81	78	84	80	78	83	80	78	76			
8	91	83	79	76	90	83	79	76	82	78	75	81	78	75	80	77	75	74			
9	88	81	76	73	87	80	76	73	79	76	73	79	75	73	78	75	72	71			
10	85	78	74	71	84	78	73	71	77	73	70	76	73	70	76	72	70	69			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	235891
5°	229936
10°	194942
15°	126351
20°	78471
25°	42232
30°	14515
35°	5849
40°	1560
45°	698
50°	273
55°	124
60°	66
65°	78
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P582957

CATALOG NUMBER: LX6C20D010 EU6209050 6LBHYLI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	376.9	27.1
10°-20°	621.6	44.7
20°-30°	322.3	23.2
30°-40°	61.0	4.4
40°-50°	7.7	0.6
50°-60°	1.1	0.1
60°-70°	0.4	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1320.7	95.0
0°-40°	1381.8	99.3
0°-60°	1390.6	100.0
0°-90°	1390.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1390.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4303	
5°	4178	377
15°	2226	622
25°	698	322
35°	87	61
45°	9	8
55°	1	1
65°	1	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P582957

CATALOG NUMBER: LX6C20D010 EU6209050 6LBHYLI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	4303.0
2.5°	4296.0
5°	4178.4
7.5°	3908.6
10°	3502.0
12.5°	2889.9
15°	2226.3
17.5°	1690.6
20°	1345.1
22.5°	1002.7
25°	698.2
27.5°	429.1
30°	229.3
32.5°	154.8
35°	87.4
37.5°	37.9
40°	21.8
42.5°	14.1
45°	9.0
47.5°	5.1
50°	3.2
52.5°	1.3
55°	1.3
57.5°	0.6
60°	0.6
62.5°	0.6
65°	0.6
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)