

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P563917

Luminaire Tested: **LX6C20D010 EX6C209030 6LBWH**

Issue Date: 2/15/2022



Test Information

Test Method: LM-79-08
Report Number: P563917
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P202739)
Test Lab: INNOVATION CENTER
Issue Date: 2/15/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX6C20D010 EX6C209030 6LBWH
Description: 6 INCH 2000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS
AND 6LBW TRIM WITH H FINISH, DIM TO WARM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1832.0 lumens
Efficiency: N/A
Efficacy: 84.0 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.16
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 21.8
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P563917

CATALOG NUMBER: LX6C20D010 EX6C209030 6LBWH

Luminous Intensity Polar Plot





TEST NUMBER: P563917

CATALOG NUMBER: LX6C20D010 EX6C209030 6LBWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	103	110	107	104	101	103	100	98	99	97	95	95	94	93	91			91
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81			81
3	98	90	84	79	96	89	83	78	86	81	77	83	79	76	81	78	75	73			73
4	92	82	75	70	90	81	75	70	79	73	69	77	72	68	75	71	67	65			65
5	86	75	68	63	84	74	68	63	72	66	62	71	65	61	69	64	61	59			59
6	80	69	62	57	78	68	61	56	67	61	56	65	60	56	64	59	55	53			53
7	75	64	56	51	73	63	56	51	62	55	51	60	55	51	59	54	50	49			49
8	70	59	52	47	69	58	51	47	57	51	46	56	50	46	55	50	46	44			44
9	66	55	48	43	65	54	47	43	53	47	43	52	47	42	51	46	42	41			41
10	62	51	44	40	61	50	44	39	50	43	39	49	43	39	48	43	39	38			38

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	61941
5°	61919
10°	61444
15°	61033
20°	60100
25°	58727
30°	55300
35°	50038
40°	41793
45°	32019
50°	22677
55°	14298
60°	8059
65°	5241
70°	3430
75°	2521
80°	1515
85°	1447



TEST NUMBER: P563917

CATALOG NUMBER: LX6C20D010 EX6C209030 6LBWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	106.7	5.8
10°-20°	302.8	16.5
20°-30°	444.0	24.2
30°-40°	462.1	25.2
40°-50°	319.7	17.5
50°-60°	139.2	7.6
60°-70°	42.7	2.3
70°-80°	12.8	0.7
80°-90°	1.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	853.5	46.6
0°-40°	1315.6	71.8
0°-60°	1774.5	96.9
0°-90°	1832.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1832.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1130	
5°	1125	107
15°	1075	303
25°	971	444
35°	748	462
45°	413	320
55°	150	139
65°	40	43
75°	12	13
85°	2	2
90°	0	



TEST NUMBER: P563917

CATALOG NUMBER: LX6C20D010 EX6C209030 6LBWH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1129.9
2.5°	1132.2
5°	1125.2
7.5°	1115.8
10°	1103.8
12.5°	1092.0
15°	1075.4
17.5°	1053.9
20°	1030.2
22.5°	1004.1
25°	970.9
27.5°	928.2
30°	873.6
32.5°	816.5
35°	747.7
37.5°	671.9
40°	584.0
42.5°	496.1
45°	413.0
47.5°	334.7
50°	265.9
52.5°	201.8
55°	149.6
57.5°	106.8
60°	73.5
62.5°	54.6
65°	40.4
67.5°	30.9
70°	21.4
72.5°	16.7
75°	11.9
77.5°	7.1
80°	4.8
82.5°	2.3
85°	2.3
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)