

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P710911

Luminaire Tested: **LD6C02D010 EU6029030 6LBHYH**

Issue Date: 10/18/2023



**Test Information**

Test Method: LM-79-08  
Report Number: P710911  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-7)  
Test Lab: INNOVATION CENTER  
Issue Date: 10/18/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD6C02D010 EU6029030 6LBHYH  
Description: 6 INCH 250 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS AND 6LCHYP TRIM WITH MW FINISH  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 260.3 lumens  
Efficiency: N/A  
Efficacy: 74.4 lumens/watt  
Spacing Criteria (0/90/45): 0.59 / 0.59 / 0.59  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 3.5  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P710911

CATALOG NUMBER: LD6C02D010 EU6029030 6LBHYH

### Luminous Intensity Polar Plot





TEST NUMBER: P710911

CATALOG NUMBER: LD6C02D010 EU6029030 6LBHYH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	115	112	110	108	112	110	108	107	106	105	103	103	101	100	99	98	98	96	96	96	96
2	110	106	103	100	108	105	102	99	102	99	97	99	97	95	96	95	93	92	92	92	92
3	106	101	97	94	105	100	96	93	97	94	92	95	93	91	93	91	89	88	88	88	88
4	103	97	92	89	101	96	92	88	94	90	87	92	89	86	90	87	86	84	84	84	84
5	99	92	88	84	97	92	87	84	90	86	83	88	85	83	87	84	82	81	81	81	81
6	95	89	84	81	94	88	83	80	86	83	80	85	82	79	84	81	79	78	78	78	78
7	92	85	80	77	91	84	80	77	83	79	76	82	79	76	81	78	76	75	75	75	75
8	89	82	77	74	88	81	77	74	80	76	73	79	76	73	78	75	73	72	72	72	72
9	86	79	74	71	85	78	74	71	77	73	71	77	73	70	76	73	70	69	69	69	69
10	83	76	71	68	83	76	71	68	75	71	68	74	71	68	73	70	68	67	67	67	67

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	37365
5°	36380
10°	31563
15°	24353
20°	16971
25°	8940
30°	2500
35°	1111
40°	551
45°	287
50°	128
55°	10
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P710911

CATALOG NUMBER: LD6C02D010 EU6029030 6LBHYH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	60.0	23.0
10°-20°	117.3	45.1
20°-30°	67.8	26.0
30°-40°	11.9	4.6
40°-50°	3.0	1.2
50°-60°	0.3	0.1
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	245.1	94.1
0°-40°	257.0	98.7
0°-60°	260.3	100.0
0°-90°	260.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	260.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	682	
5°	661	60
15°	429	117
25°	148	68
35°	17	12
45°	4	3
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P710911

CATALOG NUMBER: LD6C02D010 EU6029030 6LBHYH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	681.6
2.5°	680.5
5°	661.1
7.5°	620.5
10°	567.0
12.5°	504.5
15°	429.1
17.5°	351.5
20°	290.9
22.5°	218.5
25°	147.8
27.5°	84.6
30°	39.5
32.5°	27.0
35°	16.6
37.5°	11.0
40°	7.7
42.5°	5.3
45°	3.7
47.5°	2.4
50°	1.5
52.5°	0.6
55°	0.1
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)