

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P684914

Luminaire Tested: **LX6C25D010 EX6259027 6LBSLI**

Issue Date: 2/15/2022



Test Information

Test Method: LM-79-08
Report Number: P684914
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205419)
Test Lab: INNOVATION CENTER
Issue Date: 2/15/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX6C25D010 EX6259027 6LBSLI
Description: 6 INCH 2500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 2700K, 90CRI LEDS
AND 6LBS TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2652.1 lumens
Efficiency: N/A
Efficacy: 84.2 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 1.04
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 31.5
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P684914

CATALOG NUMBER: LX6C25D010 EX6259027 6LBSLI

Luminous Intensity Polar Plot





TEST NUMBER: P684914

CATALOG NUMBER: LX6C25D010 EX6259027 6LBSLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	107	104	101	109	105	102	99	101	99	96	97	95	93	94	92	91	89			89
2	103	96	91	86	100	94	89	85	91	87	83	88	84	81	85	82	79	77			77
3	95	86	79	74	93	85	78	73	82	76	72	79	75	71	77	73	70	68			68
4	88	78	70	64	86	77	69	64	74	68	63	72	67	62	70	65	62	60			60
5	82	71	63	57	80	70	62	57	67	61	56	66	60	55	64	59	55	53			53
6	76	64	56	51	74	63	56	51	62	55	50	60	54	50	59	53	49	47			47
7	71	59	51	46	70	58	51	45	57	50	45	55	49	45	54	49	45	43			43
8	67	54	47	41	65	54	46	41	52	46	41	51	45	41	50	45	41	39			39
9	63	50	43	38	61	50	43	38	49	42	38	48	42	37	47	41	37	36			36
10	59	47	40	35	58	46	39	35	45	39	35	45	39	34	44	38	34	33			33

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	91742
5°	90700
10°	86098
15°	79467
20°	72649
25°	65780
30°	59921
35°	55432
40°	51819
45°	48269
50°	43973
55°	38508
60°	32125
65°	25217
70°	17615
75°	9553
80°	1799
85°	0



TEST NUMBER: P684914

CATALOG NUMBER: LX6C25D010 EX6259027 6LBSLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	154.2	5.8
10°-20°	392.6	14.8
20°-30°	500.6	18.9
30°-40°	519.2	19.6
40°-50°	478.4	18.0
50°-60°	359.9	13.6
60°-70°	194.2	7.3
70°-80°	52.1	2.0
80°-90°	0.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1047.4	39.5
0°-40°	1566.6	59.1
0°-60°	2404.9	90.7
0°-90°	2652.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2652.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1674	
5°	1648	154
15°	1400	393
25°	1088	501
35°	828	519
45°	623	478
55°	403	360
65°	194	194
75°	45	52
85°	0	1
90°	0	



TEST NUMBER: P684914

CATALOG NUMBER: LX6C25D010 EX6259027 6LBSLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	1673.5
2.5°	1667.9
5°	1648.2
7.5°	1611.6
10°	1546.7
12.5°	1482.0
15°	1400.2
17.5°	1324.2
20°	1245.3
22.5°	1163.6
25°	1087.5
27.5°	1014.3
30°	946.6
32.5°	884.7
35°	828.3
37.5°	774.8
40°	724.1
42.5°	670.6
45°	622.6
47.5°	569.1
50°	515.6
52.5°	459.3
55°	402.9
57.5°	346.6
60°	293.0
62.5°	242.3
65°	194.4
67.5°	149.3
70°	109.9
72.5°	76.1
75°	45.1
77.5°	19.7
80°	5.7
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)