

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P856621

Luminaire Tested: **LD6C25D010 EU6259040 6LBWLI**

Issue Date: 2/15/2022



**Test Information**

Test Method: LM-79-08  
Report Number: P856621  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205209)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/15/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD6C25D010 EU6259040 6LBWLI  
Description: 6 INCH 2500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 4000K, 90CRI LEDS  
AND 6LBW TRIM WITH LI FINISH  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2625.0 lumens  
Efficiency: N/A  
Efficacy: 83.3 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.18  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 31.5  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P856621

CATALOG NUMBER: LD6C25D010 EU6259040 6LBWLI

### Luminous Intensity Polar Plot





TEST NUMBER: P856621

CATALOG NUMBER: LD6C25D010 EU6259040 6LBWLI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100															
1	113	110	107	104	110	107	105	103	103	101	99	100	98	97	96	95	94	92				92															
2	106	101	96	92	104	99	95	91	95	92	89	92	90	87	90	87	85	83				83															
3	100	92	87	82	97	91	86	81	88	84	80	86	82	79	83	80	77	76				76															
4	93	85	78	73	92	84	78	73	81	76	72	79	75	71	77	74	70	69				69															
5	88	78	71	66	86	77	71	66	75	70	65	73	69	65	72	68	64	63				63															
6	82	72	65	60	81	71	65	60	70	64	59	68	63	59	67	62	59	57				57															
7	77	67	60	55	76	66	59	55	65	59	54	63	58	54	62	57	54	52				52															
8	73	62	55	50	71	61	55	50	60	54	50	59	54	50	58	53	49	48				48															
9	69	57	51	46	67	57	50	46	56	50	46	55	50	46	54	49	46	44				44															
10	65	54	47	43	64	53	47	42	52	46	42	51	46	42	51	46	42	41				41															

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	89900
5°	90733
10°	93268
15°	95602
20°	97058
25°	95050
30°	89115
35°	79672
40°	64535
45°	42687
50°	21577
55°	9108
60°	2938
65°	1154
70°	962
75°	635
80°	0
85°	0



TEST NUMBER: P856621

CATALOG NUMBER: LD6C25D010 EU6259040 6LBWLI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	158.2	6.0
10°-20°	475.5	18.1
20°-30°	716.8	27.3
30°-40°	733.7	27.9
40°-50°	427.4	16.3
50°-60°	98.2	3.7
60°-70°	12.1	0.5
70°-80°	3.2	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1350.5	51.4
0°-40°	2084.1	79.4
0°-60°	2609.8	99.4
0°-90°	2625.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2625.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1640	
5°	1649	158
15°	1684	475
25°	1571	717
35°	1190	734
45°	551	427
55°	95	98
65°	9	12
75°	3	3
85°	0	0
90°	0	



TEST NUMBER: P856621

CATALOG NUMBER: LD6C25D010 EU6259040 6LBWLI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1639.9
2.5°	1636.9
5°	1648.8
7.5°	1660.7
10°	1675.5
12.5°	1678.5
15°	1684.5
17.5°	1678.5
20°	1663.7
22.5°	1616.0
25°	1571.4
27.5°	1500.0
30°	1407.8
32.5°	1312.5
35°	1190.5
37.5°	1053.5
40°	901.8
42.5°	732.1
45°	550.6
47.5°	383.9
50°	253.0
52.5°	160.7
55°	95.3
57.5°	50.6
60°	26.8
62.5°	14.9
65°	8.9
67.5°	8.9
70°	6.0
72.5°	3.0
75°	3.0
77.5°	3.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)