

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P563923

Luminaire Tested: **LX6C25D010 EX6C259030 6LBSH**

Issue Date: 2/15/2022



Test Information

Test Method: LM-79-08
Report Number: P563923
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P204188)
Test Lab: INNOVATION CENTER
Issue Date: 2/15/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX6C25D010 EX6C259030 6LBSH
Description: 6 INCH 2500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS
AND 6LBS TRIM WITH H FINISH, DIM TO WARM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2709.9 lumens
Efficiency: N/A
Efficacy: 86.0 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 31.5
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P563923

CATALOG NUMBER: LX6C25D010 EX6C259030 6LBSH

Luminous Intensity Polar Plot





TEST NUMBER: P563923

CATALOG NUMBER: LX6C25D010 EX6C259030 6LBSH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88																			
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77																			
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67																			
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58																			
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51																			
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46																			
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41																			
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37																			
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34																			
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	77697
5°	77333
10°	75733
15°	72980
20°	69627
25°	65871
30°	62136
35°	58504
40°	55089
45°	51354
50°	46821
55°	41346
60°	34997
65°	27487
70°	19619
75°	10760
80°	1894
85°	0



TEST NUMBER: P563923

CATALOG NUMBER: LX6C25D010 EX6C259030 6LBSH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	132.7	4.9
10°-20°	360.8	13.3
20°-30°	501.1	18.5
30°-40°	546.8	20.2
40°-50°	510.1	18.8
50°-60°	387.2	14.3
60°-70°	212.0	7.8
70°-80°	58.4	2.2
80°-90°	0.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	994.6	36.7
0°-40°	1541.4	56.9
0°-60°	2438.7	90.0
0°-90°	2709.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2709.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1417	
5°	1405	133
15°	1286	361
25°	1089	501
35°	874	547
45°	662	510
55°	433	387
65°	212	212
75°	51	58
85°	0	1
90°	0	



TEST NUMBER: P563923

CATALOG NUMBER: LX6C25D010 EX6C259030 6LBSH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1417.3
2.5°	1417.3
5°	1405.3
7.5°	1387.4
10°	1360.5
12.5°	1324.7
15°	1285.9
17.5°	1238.2
20°	1193.5
22.5°	1139.8
25°	1089.0
27.5°	1038.3
30°	981.6
32.5°	927.9
35°	874.2
37.5°	820.5
40°	769.8
42.5°	716.1
45°	662.4
47.5°	608.7
50°	549.0
52.5°	492.3
55°	432.6
57.5°	376.0
60°	319.2
62.5°	262.5
65°	211.9
67.5°	164.1
70°	122.4
72.5°	83.5
75°	50.8
77.5°	23.9
80°	6.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)