

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P683887

Luminaire Tested: **LX6C10D010 EX6C109030 6LBSH**

Issue Date: 2/15/2022

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P683887  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P204188)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/15/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LX6C10D010 EX6C109030 6LBSH  
Description: 6 INCH 1000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS  
AND 6LBS TRIM WITH H FINISH  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.   Condition   Description

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1073.0 lumens  
Efficiency: N/A  
Efficacy: 109.5 lumens/watt  
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 9.8  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P683887

CATALOG NUMBER: LX6C10D010 EX6C109030 6LBSH

### Luminous Intensity Polar Plot





TEST NUMBER: P683887

CATALOG NUMBER: LX6C10D010 EX6C109030 6LBSH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77			
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67			
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58			
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51			
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46			
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41			
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37			
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34			
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	30765
5°	30618
10°	29987
15°	28899
20°	27571
25°	26082
30°	24605
35°	23169
40°	21812
45°	20335
50°	18541
55°	16372
60°	13859
65°	10883
70°	7758
75°	4257
80°	758
85°	0



TEST NUMBER: P683887

CATALOG NUMBER: LX6C10D010 EX6C109030 6LBSH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	52.6	4.9
10°-20°	142.9	13.3
20°-30°	198.4	18.5
30°-40°	216.5	20.2
40°-50°	202.0	18.8
50°-60°	153.3	14.3
60°-70°	84.0	7.8
70°-80°	23.1	2.2
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	393.8	36.7
0°-40°	610.4	56.9
0°-60°	965.6	90.0
0°-90°	1073.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1073.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	561	
5°	556	53
15°	509	143
25°	431	198
35°	346	217
45°	262	202
55°	171	153
65°	84	84
75°	20	23
85°	0	0
90°	0	



TEST NUMBER: P683887

CATALOG NUMBER: LX6C10D010 EX6C109030 6LBSH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	561.2
2.5°	561.2
5°	556.4
7.5°	549.3
10°	538.7
12.5°	524.5
15°	509.2
17.5°	490.3
20°	472.6
22.5°	451.3
25°	431.2
27.5°	411.1
30°	388.7
32.5°	367.4
35°	346.2
37.5°	324.9
40°	304.8
42.5°	283.5
45°	262.3
47.5°	241.0
50°	217.4
52.5°	194.9
55°	171.3
57.5°	148.9
60°	126.4
62.5°	104.0
65°	83.9
67.5°	65.0
70°	48.4
72.5°	33.1
75°	20.1
77.5°	9.5
80°	2.4
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)