

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P856581

Luminaire Tested: **LD6C10D010 EU6109040 6LBWLI**

Issue Date: 2/15/2022

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P856581
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205209)
Test Lab: INNOVATION CENTER
Issue Date: 2/15/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD6C10D010 EU6109040 6LBWLI
Description: 6 INCH 1000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 4000K, 90CRI LEDS
AND 6LBW TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1057.0 lumens
Efficiency: N/A
Efficacy: 107.9 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.18
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 9.8
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P856581

CATALOG NUMBER: LD6C10D010 EU6109040 6LBWLI

Luminous Intensity Polar Plot





TEST NUMBER: P856581

CATALOG NUMBER: LD6C10D010 EU6109040 6LBWLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	104	110	107	105	103	103	101	99	100	98	97	96	95	94	92	92	92	92
2	106	101	96	92	104	99	95	91	95	92	89	92	90	87	90	87	85	83	83	83	83
3	100	92	87	82	97	91	86	81	88	84	80	86	82	79	83	80	77	76	76	76	76
4	93	85	78	73	92	84	78	73	81	76	72	79	75	71	77	74	70	69	69	69	69
5	88	78	71	66	86	77	71	66	75	70	65	73	69	65	72	68	64	63	63	63	63
6	82	72	65	60	81	71	65	60	70	64	59	68	63	59	67	62	59	57	57	57	57
7	77	67	60	55	76	66	59	55	65	59	54	63	58	54	62	57	54	52	52	52	52
8	73	62	55	50	71	61	55	50	60	54	50	59	54	50	58	53	49	48	48	48	48
9	69	57	51	46	67	57	50	46	56	50	46	55	50	46	54	49	46	44	44	44	44
10	65	54	47	43	64	53	47	42	52	46	42	51	46	42	51	46	42	41	41	41	41

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	36198
5°	36534
10°	37558
15°	38496
20°	39081
25°	38276
30°	35885
35°	32083
40°	25984
45°	17188
50°	8691
55°	3670
60°	1184
65°	467
70°	385
75°	254
80°	0
85°	0



TEST NUMBER: P856581

CATALOG NUMBER: LD6C10D010 EU6109040 6LBWLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	63.7	6.0
10°-20°	191.5	18.1
20°-30°	288.6	27.3
30°-40°	295.4	27.9
40°-50°	172.1	16.3
50°-60°	39.6	3.7
60°-70°	4.9	0.5
70°-80°	1.3	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	543.8	51.4
0°-40°	839.2	79.4
0°-60°	1050.9	99.4
0°-90°	1057.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1057.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	660	
5°	664	64
15°	678	191
25°	633	289
35°	479	295
45°	222	172
55°	38	40
65°	4	5
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P856581

CATALOG NUMBER: LD6C10D010 EU6109040 6LBWLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	660.3
2.5°	659.1
5°	663.9
7.5°	668.7
10°	674.7
12.5°	675.9
15°	678.3
17.5°	675.9
20°	669.9
22.5°	650.7
25°	632.8
27.5°	604.0
30°	566.9
32.5°	528.5
35°	479.4
37.5°	424.2
40°	363.1
42.5°	294.8
45°	221.7
47.5°	154.6
50°	101.9
52.5°	64.7
55°	38.4
57.5°	20.4
60°	10.8
62.5°	6.0
65°	3.6
67.5°	3.6
70°	2.4
72.5°	1.2
75°	1.2
77.5°	1.2
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)