

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P684194

Luminaire Tested: **LX6C30D010 EX6C309040 6LBNH**

Issue Date: 2/15/2022

Test Information

Test Method: LM-79-08
Report Number: P684194
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P203666)
Test Lab: INNOVATION CENTER
Issue Date: 2/15/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX6C30D010 EX6C309040 6LBNH
Description: 6 INCH 3000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 4000K, 90CRI LEDS
AND 6LBN TRIM WITH H FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1918.0 lumens
Efficiency: N/A
Efficacy: 60.7 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.84
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 31.6
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P684194

CATALOG NUMBER: LX6C30D010 EX6C309040 6LBNH

Luminous Intensity Polar Plot





TEST NUMBER: P684194

CATALOG NUMBER: LX6C30D010 EX6C309040 6LBNH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	111	108	106	111	109	106	104	104	103	101	101	99	98	97	96	95	93
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	83	79	77	75
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	65
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58
9	76	66	60	56	75	66	60	56	65	59	56	64	59	56	63	59	55	54
10	72	62	57	53	71	62	57	53	61	56	53	60	56	52	60	55	52	51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	134786
5°	131449
10°	121290
15°	107384
20°	93242
25°	79753
30°	65751
35°	43299
40°	23279
45°	10303
50°	4179
55°	3011
60°	1919
65°	1375
70°	1122
75°	741
80°	1105
85°	0



TEST NUMBER: P684194

CATALOG NUMBER: LX6C30D010 EX6C309040 6LBNH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	221.1	11.5
10°-20°	527.3	27.5
20°-30°	604.0	31.5
30°-40°	405.8	21.2
40°-50°	115.9	6.0
50°-60°	28.4	1.5
60°-70°	10.8	0.6
70°-80°	4.2	0.2
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1352.4	70.5
0°-40°	1758.2	91.7
0°-60°	1902.5	99.2
0°-90°	1918.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1918.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2459	
5°	2389	221
15°	1892	527
25°	1318	604
35°	647	406
45°	133	116
55°	32	28
65°	11	11
75°	4	4
85°	0	0
90°	0	



TEST NUMBER: P684194

CATALOG NUMBER: LX6C30D010 EX6C309040 6LBNH

CANDELA DISTRIBUTION (FULL):

	0°
0°	2458.7
2.5°	2441.2
5°	2388.7
7.5°	2294.2
10°	2178.9
12.5°	2031.9
15°	1892.1
17.5°	1745.2
20°	1598.3
22.5°	1458.4
25°	1318.5
27.5°	1189.1
30°	1038.7
32.5°	839.3
35°	647.0
37.5°	472.1
40°	325.3
42.5°	213.3
45°	132.9
47.5°	80.4
50°	49.0
52.5°	38.4
55°	31.5
57.5°	24.5
60°	17.5
62.5°	13.9
65°	10.6
67.5°	7.0
70°	7.0
72.5°	3.5
75°	3.5
77.5°	3.5
80°	3.5
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)