

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P563895

Luminaire Tested: **LX6C10D010 EX6C109030 6LBMDH**

Issue Date: 2/15/2022

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P563895  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-21)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/15/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LX6C10D010 EX6C109030 6LBMDH  
Description: 6 INCH 1000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS  
AND 6LRMD45 TRIM WITH H FINISH, DIM TO WARM  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.   Condition   Description

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 757.8 lumens  
Efficiency: N/A  
Efficacy: 77.3 lumens/watt  
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.8  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 9.8  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P563895

CATALOG NUMBER: LX6C10D010 EX6C109030 6LBMDH

### Luminous Intensity Polar Plot





TEST NUMBER: P563895

CATALOG NUMBER: LX6C10D010 EX6C109030 6LBMDH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	93			
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			
4	97	90	84	80	95	89	83	80	86	82	79	84	81	78	83	79	77	75			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70			
6	88	79	73	69	86	78	73	69	77	72	68	75	71	68	74	70	67	66			
7	84	74	68	64	82	74	68	64	72	67	64	71	67	63	70	66	63	62			
8	80	70	64	60	78	70	64	60	68	63	60	67	63	59	66	62	59	58			
9	76	66	60	56	75	66	60	56	65	60	56	64	59	56	63	59	56	54			
10	72	63	57	53	71	62	57	53	62	56	53	61	56	53	60	56	53	51			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	54601
5°	52916
10°	48724
15°	43701
20°	38888
25°	32288
30°	23073
35°	14823
40°	9031
45°	5024
50°	2226
55°	1290
60°	844
65°	610
70°	417
75°	318
80°	221
85°	126



TEST NUMBER: P563895

CATALOG NUMBER: LX6C10D010 EX6C109030 6LBMDH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	89.0	11.7
10°-20°	215.4	28.4
20°-30°	239.6	31.6
30°-40°	141.9	18.7
40°-50°	52.0	6.9
50°-60°	13.1	1.7
60°-70°	4.8	0.6
70°-80°	1.6	0.2
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	544.0	71.8
0°-40°	686.0	90.5
0°-60°	751.0	99.1
0°-90°	757.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	757.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	996	
5°	962	89
15°	770	215
25°	534	240
35°	222	142
45°	65	52
55°	14	13
65°	5	5
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P563895

CATALOG NUMBER: LX6C10D010 EX6C109030 6LBMDH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	996.0
2.5°	987.2
5°	961.6
7.5°	922.6
10°	875.3
12.5°	823.1
15°	770.0
17.5°	718.6
20°	666.6
22.5°	606.1
25°	533.8
27.5°	450.7
30°	364.5
32.5°	287.3
35°	221.5
37.5°	168.2
40°	126.2
42.5°	92.0
45°	64.8
47.5°	41.1
50°	26.1
52.5°	18.3
55°	13.5
57.5°	10.2
60°	7.7
62.5°	6.0
65°	4.7
67.5°	3.6
70°	2.6
72.5°	2.0
75°	1.5
77.5°	1.1
80°	0.7
82.5°	0.4
85°	0.2
87.5°	0.2
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)