

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P684241

Luminaire Tested: **LX6C35D010 EX6C359050 6LBSH**

Issue Date: 2/15/2022

Test Information

Test Method: LM-79-08
Report Number: P684241
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P204188)
Test Lab: INNOVATION CENTER
Issue Date: 2/15/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX6C35D010 EX6C359050 6LBSH
Description: 6 INCH 3500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 5000K, 90CRI LEDS
AND 6LBS TRIM WITH H FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3826.0 lumens
Efficiency: N/A
Efficacy: 94.7 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 40.4
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P684241

CATALOG NUMBER: LX6C35D010 EX6C359050 6LBSH

Luminous Intensity Polar Plot





TEST NUMBER: P684241

CATALOG NUMBER: LX6C35D010 EX6C359050 6LBSH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			88
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77			77
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67			67
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58			58
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51			51
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46			46
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41			41
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37			37
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34			34
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31			31

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	109695
5°	109184
10°	106929
15°	103043
20°	98300
25°	93005
30°	87729
35°	82603
40°	77781
45°	72504
50°	66104
55°	58387
60°	49415
65°	38798
70°	27681
75°	15166
80°	2683
85°	0



TEST NUMBER: P684241

CATALOG NUMBER: LX6C35D010 EX6C359050 6LBSH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	187.4	4.9
10°-20°	509.4	13.3
20°-30°	707.5	18.5
30°-40°	772.0	20.2
40°-50°	720.2	18.8
50°-60°	546.6	14.3
60°-70°	299.3	7.8
70°-80°	82.3	2.2
80°-90°	1.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1404.3	36.7
0°-40°	2176.3	56.9
0°-60°	3443.2	90.0
0°-90°	3826.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3826.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2001	
5°	1984	187
15°	1816	509
25°	1538	707
35°	1234	772
45°	935	720
55°	611	547
65°	299	299
75°	72	82
85°	0	1
90°	0	



TEST NUMBER: P684241

CATALOG NUMBER: LX6C35D010 EX6C359050 6LBSH

CANDELA DISTRIBUTION (FULL):

	0°
0°	2001.0
2.5°	2001.0
5°	1984.1
7.5°	1958.8
10°	1920.9
12.5°	1870.4
15°	1815.6
17.5°	1748.2
20°	1685.0
22.5°	1609.2
25°	1537.6
27.5°	1466.0
30°	1385.9
32.5°	1310.1
35°	1234.3
37.5°	1158.5
40°	1086.9
42.5°	1011.0
45°	935.2
47.5°	859.3
50°	775.1
52.5°	695.1
55°	610.9
57.5°	530.8
60°	450.7
62.5°	370.7
65°	299.1
67.5°	231.7
70°	172.7
72.5°	117.9
75°	71.6
77.5°	33.7
80°	8.5
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)