

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P563936

Luminaire Tested: **LX6C35D010 EX6C359030 6LBNH**

Issue Date: 2/15/2022

**Test Information**

Test Method: LM-79-08  
Report Number: P563936  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P203666)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/15/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LX6C35D010 EX6C359030 6LBNH  
Description: 6 INCH 3500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS  
AND 6LBN TRIM WITH H FINISH, DIM TO WARM  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2229.0 lumens  
Efficiency: N/A  
Efficacy: 55.2 lumens/watt  
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.84  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 40.4  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P563936

CATALOG NUMBER: LX6C35D010 EX6C359030 6LBNH

### Luminous Intensity Polar Plot





TEST NUMBER: P563936

CATALOG NUMBER: LX6C35D010 EX6C359030 6LBNH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	109	106	104	104	103	101	101	99	98	97	96	95	93			
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	83	79	77	75			
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70			
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	65			
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61			
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58			
9	76	66	60	56	75	66	60	56	65	59	56	64	59	56	63	59	55	54			
10	72	62	57	53	71	62	57	53	61	56	53	60	56	52	60	55	52	51			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	156643
5°	152762
10°	140957
15°	124796
20°	108358
25°	92685
30°	76410
35°	50319
40°	27051
45°	11978
50°	4853
55°	3498
60°	2226
65°	1596
70°	1314
75°	868
80°	1294
85°	0



TEST NUMBER: P563936

CATALOG NUMBER: LX6C35D010 EX6C359030 6LBNH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	256.9	11.5
10°-20°	612.8	27.5
20°-30°	702.0	31.5
30°-40°	471.6	21.2
40°-50°	134.7	6.0
50°-60°	33.0	1.5
60°-70°	12.6	0.6
70°-80°	4.9	0.2
80°-90°	0.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1571.7	70.5
0°-40°	2043.3	91.7
0°-60°	2211.0	99.2
0°-90°	2229.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2229.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2857	
5°	2776	257
15°	2199	613
25°	1532	702
35°	752	472
45°	154	135
55°	37	33
65°	12	13
75°	4	5
85°	0	1
90°	0	



TEST NUMBER: P563936

CATALOG NUMBER: LX6C35D010 EX6C359030 6LBNH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2857.4
2.5°	2837.1
5°	2776.0
7.5°	2666.2
10°	2532.2
12.5°	2361.4
15°	2198.9
17.5°	2028.2
20°	1857.4
22.5°	1694.9
25°	1532.3
27.5°	1381.9
30°	1207.1
32.5°	975.4
35°	751.9
37.5°	548.7
40°	378.0
42.5°	247.9
45°	154.5
47.5°	93.4
50°	56.9
52.5°	44.7
55°	36.6
57.5°	28.5
60°	20.3
62.5°	16.2
65°	12.3
67.5°	8.2
70°	8.2
72.5°	4.1
75°	4.1
77.5°	4.1
80°	4.1
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)